
## 产品规格

Product specification

产品名称	浴室魔音灯	产品型号	D39	
Prode cthame	Bathroom magic sound lamp	It enmodel number		
产品寿命	10000小时以上	光源颜色 Li ghsource color	白、绿、黄 White, green, yellow	
产品尺寸	76* <b> </b>	蓝牙 版	蓝牙5.2	
P radu cóize		Bl etc othweon	Bluetooth 5.2	
使用场景	浴室、家居、车内等	光源类型	LED	
U esagenarios	B afform, home, car, etc	Light source type		
工作 温度 Operati ng ter ripectre	-20°C~70°C	音乐播放	TF卡或蓝牙 TF card or Bluetoot h	
工作电压	5V	防水等级	IP65级防尘防水	
Operat ingV oltge		M siapl shock	TF car & Bluetooth	
电 溶量	1100mA	线 路连接	标准Type-C接口	
b atterapacity	1100mA	Line connection		

## 灯光颜色











## D39款浴室魔音灯

39 Bathroom magic sound lamp



## 使用说明书 an instruction manual

## 产品描述


Product description

浴室魔音灯专为浴室而生,它采用华丽帷美的LED光源,亮彩夺目,打造绚丽舞台灯光。蓝牙音箱+IP65级防水+声控彩灯为您带来不一样的使用体验,使用范围不仅可以在浴室,底部的吸盘还可以吸附在任意的光滑平面上,如:瓷砖、玻璃等。

The bathroom magic light is designed for the bathroom. It uses a gorgeous and beautiful LED light source, which is bright and dazzling to create a gorgeous stage lighting. Bluetooth speakers + IP65 waterproof + voice-activated lights bring you a different experience. The scope of use can not only be in the bathroom, but the suction cup at the bottom can also be adsorbed on any smooth surface. Such as: tiles, qlass, etc.

## 按键功能





② 单按降低音量,长按切换上一曲 Raise the volume or switch to the next song

- 单按暂停播放(在5秒无操作进 入休眠的情况下单击为唤醒), 长按开关机;
- 4 单按增加音量,长按切换下一曲
- 5 打开和关闭DJ灯光 Tum the lights on or off

## 产品细节

1触摸按键

浴室魔音灯操作简单,通过单击或长按轻松掌控魔音灯。 但是在5秒无操作的情况下按键功能进入休眠模式(音乐照常播放,灯光照常闪耀)。只需单击一下任意按键便可再次唤醒—— 唤醒后再操作一下唤醒的按键——便可操作其他按键。

②USB充电


浴室魔音灯使用标准Type-C接口充电,和市面主流手机配置相同,一线两用,充电更简单。






#### ③吸盘吸附固定

浴室魔音灯使用透明吸盘吸附, 超稳固定。吸力大, 不易掉落, 拽都拽不下来! 放心摇摆! 使用场景广泛, 如图所示。










#### PRODUCT SPECIFICATIONS

Product name	Bathroom magic sound lamp	Item model number	D39
Product life	10000hours or more	Light source color	White, green, yellow
Product Size	76*Φ85mm	Bluetooth version	Bluetooth 5.2
Usage scenarios	Bathroom, home, car, etc	Light source type	LED
Operating temperature	-20℃~70℃	Music playback	TF card or Bluetooth
Operating Voltage	5V	Music playback	TF card or Bluetooth
battery capacity	1100mA	Lineconnection	Type-C interface

#### THE COLOR OF THE LIGHT









# an instruction manual

D39 Bathroom magic sound lamp

#### PRODUCT DESCRIPTION

The bathroom magic light is designed for the bathroom. It uses a gorgeous and beautiful LED light source, which is bright and dazzling to create a gorgeous stage lighting. Bluetooth speakers + IP65 waterproof + voice-activated lights bring you a different experience. The scope of use can not only be in the bathroom, but the suction cup at the bottom can also be adsorbed on any smooth surface. Such as: tiles, glass, etc.

#### **KEY FUNCTION**

1 Mode selection button, to switch TF card or Bluetooth TF card playback, you need to disconnect the Bluetooth connection first.



- 2 Single press to decrease the volume, long press to switch to the next song
- 3 Single press to pause playback (click to wake up after 5 seconds of inactivity) and long press to turn on and off;
- Single press to increase volume, long press to switch to previous song
- 5 Turn DJ lights on and off

#### TOUCH BUTTON

**1**Touch button

The bathroom magic sound light is easy to operate, and you can easily control the magic sound light with a single click or long press.

Product lighting effects

But in the case of no operation for 5 seconds, the key function enters sleep mode (the music is still playing, and the lights are still shining). Just click any key to wake up again—wake up and then operate the wake-up key—you can operate other keys.

#### **2USB** charging

The bathroom magic sound lamp uses the standard Type-C interface to charge, which is the same as the mainstream mobile phone configuration in the market.





### 3Suction cup fixed

The magic sound lamp in the bathroom is adsorbed by a transparent suction cup, which is super stable and fixed. It has strong suction and is not easy to fall. The usage scenarios are extensive,









#### FCC WARNING

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- —Reorient or relocate the receiving antenna.
- —Increase the separation between the equipment and receiver.
- —Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- —Consult the dealer or an experienced radio/TV technician for help.

Note: The Grantee is not responsible for any changes or modifications not expressly approved by the party responsible for compliance. such modifications could void the user's authority to operate the equipment.

The device has been evaluated to meet general RF exposure requirement.

This equipment complies with FCC's RF radiation exposure limits set forth for an uncontrolled environment. This device and its antenna(s) must not be co-located or conjunction with any other antenna or transmitter.

The device can be used in portable exposure condition without restriction.