

# Bambu Lab X1& X1-Carbon 30 Printer Quick Start

Please review the entire guide before operating the printer.

\* Safety Notice: Do not connect to power until the assembly is complete.



### **Component Introduction**




## **Accessory Specification**



**Touch Screen** 







250g Filament



Spare Hot End




Nozzle Wiping Pad (x2)



Power Cord

**Unclogging Pin Tool** 




**PTFE** Tube





Allen Key H1.5 Allen Key H2

Glue Stick for Build Plate






**Bambu Scraper** 


Spare Sheet for Bambu Cool Plate (x2)

**Flexible Build Plate** 


## **Tool Head Unlock**




#### **Screen Installation**



Pull the flat flex cable out about 50mm.




Insert the flat flex cable into the port by pressing the terminal as pictured.




Insert the screen back to the slot on the printer, then lock it by pushing it to the left.

# Spool Holder Assembly




Remove the screw as pictured.




Screw the spool holder onto the hole sites as pictured.

#### **Hot Bed Unlock**



Remove the three screws to unlock the hot bed. Connect the printer to power. Follow the instructions on the screen to complete the initial calibration. Remove the protective foam beneath the hot bed when calibration is complete.

# **Filament Loading**



Insert the filament into the PTFE Tube. Keep pushing the filament until it can not move forward.

## Specification

Technology		X1-Carbon	X1
		Fused Deposition Modeling	
Body	Build Volume(W*D*H)	256*256*256 mm	
	Chassis	Steel	
	Shell	Aluminum & Glass	Polycarbonate & Glas
Tool Head	Hot End	All-Metal	
	Extruder Gears	Hardened Steel	Steel
	Nozzle	Hardened Steel	Stainless Steel
	Max Hot End Temperature	300°C	
	Nozzle Diameter (Included)	0.4 mm	
	Nozzle Diameter (Optional)	0.2 mm, 0.6 mm, 0.8 mm	
	Filament Cutter	Yes	
	Filament Diameter	1.75 mm	
Hot bed	Build Plate	Flexible Steel Plate	
	Build Plate Surface(Included)	Bambu Cool Plate, Bambu Engineering Plate	
	Build Plate Surface (Optional)	Bambu Hot Plate	
	Max Build Plate Temperature	120°C	
Speed	Max Speed of Tool Head	500 mm/s	
	Max Acceleration of Tool Head	20 m/s^2	
	Max Hot End Flow	32 mm^3/s @ABS	
Cooling	Part Cooling Fan	Closed Loop Control	
	Hot End Fan	Closed Loop Control	
	Control Board Fan	Closed Loop Control	
	Chamber Temperature Regulator Fan	Closed Loop Control	
	Auxiliary Part Cooling Fan	Closed Loop Control	Optional
	Air Filter	Activated Carbon Filter	Optional
Supported Filament	PLA, PETG, TPU,ABS,ASA,PVA,PET	Yes	
	PA, PC	Ideal	Capable
	Carbon/Glass Fiber Reinforced Polymer	Ideal	Not Recommended
Sensors	Bambu Micro Lidar	Yes	
	Chamber Monitoring Camera	1920*1080 Included	Optional
	Door Sensor	Yes	
	Filament Run Out Sensor	Yes	
	Filament Odometry	Optional with AMS	
	Power Loss Recover	Yes	
Physical Dimensions	Dimensions	389*389*457mm	
	Net Weight	14.13kg	13.18kg


Electrical Requirements	Voltage	100-240 VAC, 50/60 Hz	
	Max Power	1000W@220V, 350W@110V	
Electronics	Display	5-inch 1280*720 Touch Screen	
	Connectivity	Wi-Fi,Bambu Bus	
	Storage	4GB EMMC and Micro SD Card Reader	
	Control Interface	Touch Screen, APP, PC Application	
	Motion Controller	Dual-Core Cortex M4	
	Application Processor	Quad ARM A7 1.2 GHz	
	Neural-Network Processing Unit	2 Tops	
Software	Slicer	Bambu Studio, Cura, Superslicer	
	Slicer Supported OS	MacOS, Windows	
Wifi	Frequency Range	2400MHz-2483.5MHz	
	Transmitter Power (EIRP)	≤ 21.5dBm(FCC) ≤ 20 dBm (CE/SRRC)	
	Protocol	802.11b/g/n	
	Wavelength	405nm, 808nm	
Laser	Transmitter Power	≤ 5mW	
	Maximum Output of Laser Radiation	<0.39mW	


Enjoy!

If you run into any issues during the guided setup, we are here to help. customersupport@bambulab.com



www.bambulab.com







Hereby, Sherzhen Tuzzhu Technology Co., Ltd. dedares that the radio equipment type X1/X1-Carbon is in complement with Radio Expirement Regulations 2017. The full bear of the GB detaration of conformity is available at the following internet address: www.barblub.com/euro-complemeet

Complies with 21 CFR 1040 10 and 1040.11 except for conformance with IEC 60825–1 Ed.3, as described in Laser Notice No.56,dated May 8,2019

) M

反画