


# 2.4GHz 1608 Chip Antenna: RANT1608F245C01



## Application:

WLAN, 802.11b/g, Bluetooth, WLAN, etc...

## Features

SMD, high reliability, ultra Impact, Omni-directional...

## Part number Information

RANT 1608 F 245 C 01  
(A) (B) (C) (D) (E) (F)


(A)Product Type	Chip Antenna
(B) Size Code	1.6x0.8mm(±0.1mm)
(C) Material	High K material
(D) Frequency	2.4 ~ 2.5GHz
(E) Feeding mode	PIFA & Single Feeding
(F) Antenna type	Type=01

## Electrical Specification

Working Frequency Range	2400 ~2500 MHz
Bandwidth	120 MHz (Min.)
Peak Gain	3.35 dBi (Typ.)
Impedance	50 Ohm
Return loss	10 dB ( Min)
Polarization	Linear
Azimuth Beamwidth	Omni-directional
Operation Temperature(°C)	-40 ~85 °C
Resistance to Soldering Heats	10sec. ( @ 280°C)
Termination	Ni / Au (Leadless)

The specification is defined on EVB.


## Dimension and Terminal Configuration



Dimension (mm)	
L	1.60 ± 0.10
W	0.80 ± 0.10
T	0.80 ± 0.10


No.	Terminal Name
1	Feeding/GNG
2	GND/Feeding

## Evaluation Board Reference




### 设计标准:


1. 图示中的尺寸为标准封装，仅作为参考；净空区的尺寸会根据每个版型进行调整和优化。
2. 天线最优放置于PCBA的中间区域；天线及其板后的匹配物料最优放置于板边缘。
3. 净空区周围需一排过孔，与PCBA上的其它回路或物料进行隔离。
4. G最优为1.5~2mm, W最优为3~5mm, L最优为4~6mm, D最优为0.5~1mm。
5. 天线性能与版型、组装、佩戴等相关，因而各版型的性能会有所不同。



### 设计指导:

- 1、原则上，净空区左侧边缘距离板边的间距L1应该尽量大，且注意与底部电池的间距。
- 2、净空区的宽度W最优为1.5mm~2mm。
- 3、净空区的长度L2的长度为2mm~4mm。







## Electrical Characteristics

### Return Loss & Radiation

## ELECTRICAL CHARACTERISTICSS11



## Radiation Pattern





## Radiation

## Electrical Characteristics

	Feature	Specification
1	Central frequency	2445MHz
2	Bandwidth	>100MHz
3	Peak gain	>3dBi
4	VSWR	<2
5	Polarization	Linear
6	Azimuth beamwidth	Omnidirectional
7	Impedance	50 $\Omega$

**Taping Specifications**

Reel and Taping Specification																																			
<p><b>Reel Specification</b></p> <div style="text-align: center;">  <p>7" x 8 mm</p> <table border="1" style="margin: 20px auto; border-collapse: collapse; text-align: center;"> <thead> <tr style="background-color: #e0e0e0;"> <th style="padding: 5px;">TYPE</th> <th colspan="2" style="padding: 5px;">SIZE</th> <th style="padding: 5px;">A</th> <th style="padding: 5px;">B</th> <th style="padding: 5px;">C</th> <th style="padding: 5px;">D</th> </tr> </thead> <tbody> <tr> <td style="padding: 5px;">1608</td> <td style="padding: 5px;">7"</td> <td style="padding: 5px;">4K/Reel</td> <td style="padding: 5px;"><math>4.0 \pm 0.5</math></td> <td style="padding: 5px;"><math>4.0 \pm 2</math></td> <td style="padding: 5px;"><math>13.5 \pm 0.5</math></td> <td style="padding: 5px;"><math>178 \pm 2</math></td> </tr> </tbody> </table> </div>												TYPE	SIZE		A	B	C	D	1608	7"	4K/Reel	$4.0 \pm 0.5$	$4.0 \pm 2$	$13.5 \pm 0.5$	$178 \pm 2$										
TYPE	SIZE		A	B	C	D																													
1608	7"	4K/Reel	$4.0 \pm 0.5$	$4.0 \pm 2$	$13.5 \pm 0.5$	$178 \pm 2$																													
<p><b>Tapping Specification</b></p> <div style="text-align: center;">  </div> <table border="1" style="margin: 20px auto; border-collapse: collapse; text-align: center;"> <thead> <tr style="background-color: #e0e0e0;"> <th style="padding: 5px;">Packaging</th> <th style="padding: 5px;">Type</th> <th style="padding: 5px;">A</th> <th style="padding: 5px;">B</th> <th style="padding: 5px;">W</th> <th style="padding: 5px;">E</th> <th style="padding: 5px;">F</th> <th style="padding: 5px;">G</th> <th style="padding: 5px;">H</th> <th style="padding: 5px;">T</th> <th style="padding: 5px;"><math>\psi D</math></th> <th style="padding: 5px;">P</th> </tr> </thead> <tbody> <tr> <td style="padding: 5px;">Paper Type</td> <td style="padding: 5px;">1608</td> <td style="padding: 5px;"><math>1.90 \pm 0.20</math></td> <td style="padding: 5px;"><math>3.50 \pm 0.20</math></td> <td style="padding: 5px;"><math>8.0 \pm 0.20</math></td> <td style="padding: 5px;"><math>1.75 \pm 0.10</math></td> <td style="padding: 5px;"><math>3.5 \pm 0.05</math></td> <td style="padding: 5px;"><math>4.0 \pm 0.10</math></td> <td style="padding: 5px;"><math>2.0 \pm 0.05</math></td> <td style="padding: 5px;"><math>0.75 \pm 0.10</math></td> <td style="padding: 5px;"><math>1.50 \pm 0.10</math></td> <td style="padding: 5px;"><math>4.0 \pm 0.1</math></td> </tr> </tbody> </table>												Packaging	Type	A	B	W	E	F	G	H	T	$\psi D$	P	Paper Type	1608	$1.90 \pm 0.20$	$3.50 \pm 0.20$	$8.0 \pm 0.20$	$1.75 \pm 0.10$	$3.5 \pm 0.05$	$4.0 \pm 0.10$	$2.0 \pm 0.05$	$0.75 \pm 0.10$	$1.50 \pm 0.10$	$4.0 \pm 0.1$
Packaging	Type	A	B	W	E	F	G	H	T	$\psi D$	P																								
Paper Type	1608	$1.90 \pm 0.20$	$3.50 \pm 0.20$	$8.0 \pm 0.20$	$1.75 \pm 0.10$	$3.5 \pm 0.05$	$4.0 \pm 0.10$	$2.0 \pm 0.05$	$0.75 \pm 0.10$	$1.50 \pm 0.10$	$4.0 \pm 0.1$																								


## 2.4GHz 1608 Chip Antenna: RANT1608F245C01



### Reliability Table

Test Item	Procedure	Requirements Ceramic Type	Remark (Reference)
<b>Electrical Characterization</b>		Fulfill the electrical specification	User Spec.
<b>Thermal Shock</b>	<ol style="list-style-type: none"> <li>Preconditioning: 50 ± 10°C / 1 hr , then keep for 24 ± 1 hrs at room temp.</li> <li>Initial measure: Spec: refer Initialspec.</li> <li>Rapid change of temperature test: -30°C to +85°C; 100 cycles; 15 minutes at Lower category temperature; 15 minutes at Upper category temperature.</li> </ol>	No Visible Damage. Fulfill the electrical specification.	MIL-STD-202 107
<b>Temperature Cycling</b>	<ol style="list-style-type: none"> <li>Initial measure: Spec: refer Initialspec.</li> <li>100 Cycles (-30°C to +85°C), Soak Mode=1 (2 Cycle/hours).</li> <li>Measurement at 24 ± 2Hours after test condition.</li> </ol>	No Visible Damage. Fulfill the electrical specification.	JESD22 JA104
<b>High Temperature Exposure</b>	<ol style="list-style-type: none"> <li>Initial measure: Spec: refer Initialspec.</li> <li>Unpowered; 500hours @ T=+85°C.</li> <li>Measurement at 24 ± 2 hours aftertest.</li> </ol>	No Visible Damage. Fulfill the electrical specification.	MIL-STD-202 108
<b>Low Temperature Storage</b>	<ol style="list-style-type: none"> <li>Initial measure: Spec: refer Initialspec.</li> <li>Unpowered: 500hours @ T=-30°C.</li> <li>Measurement at 24 ± 2 hours aftertest.</li> </ol>	No Visible Damage. Fulfill the electrical specification.	MIL-STD-202 108
<b>Solderability (SMD Bottom Side)</b>	Dipping method: <ol style="list-style-type: none"> <li>Temperature: 235 ± 5°C</li> <li>Dipping time: 3 ± 0.5s</li> </ol>	The solder should cover over 95% of the critical area of bottom side.	IEC 60384-21/22 4.10
<b>Soldering Heat Resistance (RSH)</b>	Preheating temperature: 150 ± 10°C. Preheating time: 1~2 min. Solder temperature: 260 ± 5°C. Dipping time: 5 ± 0.5s	No Visible Damage.	IEC 60384-21/22 4.10
<b>Vibration</b>	5g's for 20 min., 12 cycles each of 3 orientations Note: Use 8"X5" PCB .031" thick 7 secure points on, one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10-2000 Hz.	No Visible Damage.	MIL-STD-202 Method 204
<b>Mechanical Shock</b>	Three shocks in each direction shall be applied along the three mutually perpendicular axes of the test specimen (18 shocks) Peak value: 1,500g's Duration: 0.5ms Velocity change: 15.4 ft/s Waveform: Half-sine	No Visible Damage.	MIL-STD-202 Method 213
<b>Humidity Bias</b>	<ol style="list-style-type: none"> <li>Humidity: 85% R.H., Temperature: 85 ± 2 °C.</li> <li>Time: 500 ± 24 hours.</li> <li>Measurement at 24 ± 2hrs after test condition.</li> </ol>	No Visible Damage. Fulfill the electrical specification.	MIL-STD-202 Method 106

## 2.4GHz 3216 Chip Antenna: RANT1608F245C01

<b>Board Flex (SMD)</b>	<p>1. Mounting method: IR-Reflow. PCB Size (L:100 × W:40 × T:1.6mm)</p> <p>2. Apply the load in direction of the arrow until bending reaches 2 mm.</p>	<p>No Visible Damage.</p>	<p>AEC-Q200 005</p>
<b>Adhesion</b>	<p>Force of 1.8Kg for 60 seconds.</p> 	<p>No Visible Damage Magnification of 20X or greater may be employed for inspection of the mechanical integrity of the device body terminals and body/terminal junction.</p>	<p>AEC-Q200 006</p>
<b>Physical Dimension</b>	<p>Any applicable method using x10 magnification, micrometers, calipers, gauges, contour projectors, or other measuring equipment, capable of determining the actual specimen dimensions.</p>	<p>In accordance with specification.</p>	<p>JESD22 JB100</p>

### Revision History

Revision	Date	Content
1	2019/03/01	New Datasheet
2	2020/02/22	Add 2D radiation characteristic