

12 FCC Warning

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions:
(1) This device may not cause harmful interference, and
(2) This device must accept any interference received, including interference that may cause undesired operation.

Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

Note: This equipment has been tested and found to comply with the limits for a Class B digital device pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference to other licensed operations. However, this equipment may cause interference to other licensed operations, especially radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment to an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

This equipment complies with FCC radiation exposure limits set forth for an uncontrolled environment. This equipment should be installed and operated with minimum distance 20cm between the radiator and your body.

11 IC Warning

This device complies with Industry Canada's Interference-free (MIS) standards. Operation is subject to the following two conditions:

- (1) This device may not cause interference, and
- (2) This device must accept any interference received, including interference that may cause undesired operation of the device.

A product approved for sale in Canada must also be approved for sale in the United States.

- (1) Repaired and/or replaced with a new unit.
- (2) Repaired and/or replaced with a new unit.

This device is a digital apparatus compliant with Canadian ICES-003.

Cet appareil numérique de la classe B est conforme à la norme NMB-003 du Canada.

When using the product, maintain a distance of 20cm from the body to ensure compliance with RF exposure requirements.

Declaration F-107
Conformité de l'appareil au produit, maintenance et distance de 20 cm du corps.

Conformité de l'appareil au produit, maintenance et distance de 20 cm du corps.

09 Warranty Policy

Warranty Period: One Year. *The warranty period commences the date of purchase.
Shanghai Catlink Intelligent Technology Co., Ltd. warrants the device against defects in materials and workmanship under ordinary consumer use for one year from the date of original purchase.

Non-Warranty:
1- Defects caused by incorrect installation, improper use, or malicious tampering.

- 2- Malfunctions caused by incorrect installation, improper use, or malicious tampering.
- 3- Damage caused by force majeure.

4- Out of warranty period. 5- No valid proof of purchase.

10 Customer Service

We will provide customers with a one-year free warranty service.

If you have questions or need assistance, contact us!

Phone Support
+1 833 440 2772-6974 EST

Email Support
support@catlink.cn 24/7

08 Detailed Hazard Data

Component	Hazardous Substances					RoHS (2002/95/EC)	REACH (2006/1825/EC)
	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent Chromium (Cr(VI))	Polychlorinated Biphenyls (PCBs)		
Printed Circuit Board (PCB)	X	O	O	O	O	O	O
Plastic	O	O	O	O	O	O	O
Glass	O	O	O	O	O	O	O
Metal	O	O	O	O	O	O	O
Adapter	O	O	O	O	O	O	O

This table is prepared in accordance with the provisions of EU Directive 2002/95/EC.

O: below the limit requirements specified in EU Directive 2002/95/EC.


X: above the limit requirements specified in EU Directive 2002/95/EC.

07 Product Information

Name	Catlink Smart Pet Drier
Model	C-0001, C-0002, C-0003, C-0004, C-0005, C-0006, C-0007, C-0008, C-0009
Main Material	ABS, Tempered Glass
Applicable	Cat or Small Dogs
Weight	5.1 kg
Standard	GB4706.1-2005, GB4706.19-2008
Dimensions	487 x 278 x 448 mm
Voltage	220 V
Power	1000 W
Operating Temperature	15 ~ 35 °C
Wireless Connection	Bluetooth
Version	V 1.0.1



SMART PET DRYER USER MANUAL




Please read carefully and keep for future reference.

01 Important Safety Instructions


Failure to comply with the following conditions may result in product malfunctions or unexpected damages.

- The drying function must only be used under the supervision of the user manual.
- If your pet has any physical or psychological health concerns, consult a professional veterinarian before using the device.
- Do not use the device with your pet in a vehicle.
- Keep items such as towels, pillows, or cushions away from the device to prevent air-waves from getting mixed, which can affect temperature and airflow.
- Do not use the device with your pet in a confined space.
- Place the device on a hard, cold surface, and avoid flammable or soft objects.
- This device is suitable for cats (over 6 months) and small dogs.
- Do not use the device with your pet in a confined space.
- Contact the manufacturer immediately if you notice any unusual humming or unusual sounds from the device. When the device is not in use, turn it off and unplug it.
- Do not place items on top of the device and keep both the interior and exterior clear and dry.
- Do not use the ozone disinfection function when pets are inside the device. Do not use the ozone disinfection function when animals are present in the room.
- Use the digital timer when the power button is pressed.
- Leave a 10cm space when placing the device against a wall.
- Do not disassemble, modify, or attempt to repair the device or your own, as it may void all warranty and safety.
- For any doubts, feel free to contact customer service support.

02 Product



03 Buttons and Display



04 Operation Instructions

First-time Usage: Turn on the power switch. The default mode is Comfort Drying. The device will start drying your pet's fur. After drying, the device will automatically turn off. Please refer to the user manual for more details.

Mode Switch: After unlocking, press the pause button to stop, and press the Mode select button to switch drying modes.

Ozone Disinfection: After unlocking, press the on/off button and the Mode select button at the same time to start. Do not use the ozone disinfection function when pets are inside the device. Do not use the ozone disinfection function in a confined space. Please refer to the user manual for more details.

Customization: For Bluetooth version, personalize temperature, time, and speed settings through the app.

-C / F°: After unlocking, long press the Mode select button for 5 seconds to switch between Celsius/Fahrenheit.

White - Running normally
Red - Operating abnormally

05 Installation and Usage

To ensure the safety of your pet and proper usage, the device is delivered in its inactive state. Please download and install the CATLINK APP and follow the product instructions.



Scan to download CATLINK APP



Scan QR code to access installation and usage instructions.

06 Maintenance



Scan to download CATLINK APP



Scan QR code to access installation and usage instructions.

This product complies with the radio interference requirements of the European Community.

Product name: Catlink smart pet dryer

Product model: C L - D A - 0 2

Manufacturer: Shanghai Catlink Intelligent Technology Co.,Ltd

Address: N o . 8 0 0 N a x i a n r o a d , P u d o n g n e w d i s t r i c t , S h a n g h a i , C h i n a

Frequency Range: 2402MHz to 2480MHz

Max. output Power: 1.26 **dbm**

SIMPLIFIED EU DECLARATION OF CONFORMITY

The simplified EU declaration of conformity referred to in Article 10(9) shall be provided as follows:

Hereby, [Shanghai Catlink Intelligent Technology Co., Ltd](#) declares that radio equipment type C L - D A - 0 2 is in compliance with Directive 2014/53/EU, and this product is allowed to be used in all EU member states.

The full text of the EU declaration of conformity is available at following

This product can be used across EU member states.