

VUSION Bluetooth LE

Product Specification

SES-IMAGOTAG

Read all documents and system instructions carefully to minimize the risk of injuring persons and to avoid damage to the system or damage to the environment. Always keep all documents and guidance accessible.

If necessary, the content of this document will be updated. You can request the latest version of the document via pdm.hardware@ses-imagotag.com.

About ESLs

An electronic shelf label is a device that shows article data and price information on its display. In comparison to printed labels the information is automatically updated if price or article data changes.

In this product specification the focus is set on the product family VUSION Bluetooth LE. With its new Bluetooth LE wireless signal range it is a new product range, and the line-up has the display sizes 1.5", 1.6", 2.1", 2.2", 2.6", 4.2" and 7.4".

General Key Features

- Bluetooth LE proprietary radio protocol
- Radio coverage: up to 25 meters
- Bi-directional communication
- Ultra-low power consumption
- Full graphical e-Ink display with paper-like readability
- Super wide viewing angle (nearly 180 degrees)
- Flexible mounting options available
- May be used in landscape and portrait mode
- Fast response time
- 128-bit AES encryption
- Multiple pages support with preloading and fast page switching
- Integrated Passive NFC tag

The installation instructions are intended for trained electricians who can exhibit the following qualifications:

- Knowledge of the use of tools and work instructions.
- Knowledge of the usable conditions of the tool.
- Knowledge of the electrical safety instructions.
- Knowledge of the electrical building regulations.
- Knowledge of the relevant standards.
- Knowledge of the assembly schedule.

Overview about VUSION Engage labels

Product name	Model	Resolution	DPI	Display colors	Usable pages	Battery Type	IP rating
VUSION 1.5	EDB1-0150-A	200x200	186	b/w/r	2	Coin Cell (CR2450)	IP53
VUSION 1.6	EDB1-0160-A	152x152	140	b/w/r	2	Coin Cell (CR2450)	IP53
VUSION 2.1	EDB1-0210-A	248x128	135	b/w/r	2	Coin Cell (CR2450)	IP53
VUSION 2.1 WP	EWB1-0210-A	248x128	135	b/w/r	2	Coin Cell (CR2450)	IP68
VUSION 2.2	EDB1-0220-A EDB1-0220-B	212x104	111	b/w/r	2	Coin Cell (CR2450)	IP53
VUSION 2.6	EDB1-0260-A	296x152	125	b/w/r	2	Coin Cell (CR2450)	IP53
VUSION 4.2 WP	EWB1-0420-A	400x300	120	b/w/r	2	Coin Cell (CR2450)	IP68
VUSION 7.4	EDB1-0740-A	480x800	126	b/w/r	2	Coin Cell (CR2450)	IP53

General remarks

The SES-imagotag VUSION Labels must be installed according to the mounting instructions of the producer. In rare cases it may occur that the usage of wireless appliances is restricted by the building owner (e.g. Airport or Hospital). Please contact the appropriate authorities before installing the SES-imagotag VUSION Labels.

Environmental

General

E-Paper displays are moisture and UV sensitive. The absolute rating operating environments describes the boundary conditions for updating the display while the absolute rating storage environment (see Storage and warehousing) describes the boundary conditions for a display not updating.

	BWR R2.0	BW
Operating temperature	0° C to +40° C	-25°C - 10°C

Cleaning Instructions

Clean the electronic label with the help of a damp cloth. Use only common household cleaners.

Do not clean the label with alcohol, solvents and / or abrasive cleaning products.

Note: Do not use liquid or aerosol cleaners and keep it away from water.

Temperature and Humidity Conditions

High humidity combined with low temperature are not recommended.

Low temperature will reduce the battery lifetime.

Storage and warehousing

While displays are rated to perform according to specification for the warranty period at the absolute specified operating environment, the better the storage condition, the better the E-Paper displays will perform. Like other moisture and UV sensitive components, we recommend that our labels are stored in temperature and humidity-controlled environments, and whenever possible, under below defined Optimal Storage Conditions, away from sunlight, to optimize their performance.

It is strongly recommended to observe the following points to ensure the best operation, functioning and battery lifetime:

Storage temperature and humidity

	BWR	BW
Storage temperature	-20° C to +50° C	-20° C to +50° C
Storage humidity	40% - 70%	40% - 70%

Intended Use

The VUSION electronic shelf label family is exclusively designed to connect to Access Points of the company SES-imagotag or acknowledged partners via radio.

The device may only be used in areas where the environmental fulfill the requirements described in the chapter “**Environmental**”.

Cleaning Instructions

Clean the electronic label with the help of a damp cloth. Use only common household cleaners. Do not clean the label with alcohol, solvents and / or abrasive cleaning products.

Note: Do not use liquid or aerosol cleaners and keep it away from water.

Improper use

SES-imagotag shall not be responsible for defects resulting:

- from use or storage which is harmful to the proper working of the product (e.g. abnormal use, incorrect maintenance and/or storage) and/or non-compliance with the applicable product environment specifications
- from a use of the product which does not comply with the recommendations and specifications of SES-imagotag
- from use or installation which is not compliant with the applicable functional description, or any other technical specifications provided by SES-imagotag

Please note the following handling instructions, non-compliance is considered improper use:

- Don't drop VUSION Family Labels.
- Keep VUSION Family Labels away from water.
- Don't use the VUSION Labels with defective parts.
- Don't use the VUSION Labels with spare parts and accessories which are not examined and approved by SES-imagotag.
- Unauthorized changes or modifications to the VUSION Labels and their components without the consent of SES-imagotag are strictly forbidden.
- The SES-imagotag VUSION Labels do not contain parts, except batteries, that are allowed to be maintained by the user.
- The SES-imagotag VUSION Labels must NOT be dismantled. For necessary maintenance or repair works always contact the manufacturer.





- Don't throw VUSION Labels into the dustbin. Deposit VUSION Labels at a reprocessing company.
- Contact SES-imagotag for more details about the removal process.
- Please do not use any liquid or spray cleaners directly on the surface of the VUSION Labels.
- SES-imagotag takes no responsibility for stolen VUSION Labels without encryption.
- **WARNING:** Contains lithium pouch or cell batteries
- **NEW AND USED BATTERIES CAN BE HAZARDOUS, KEEP THEM OUT OF REACH OF CHILDREN**
- Swallowing or placing batteries inside any part of the body may lead to severe or fatal injuries within 2 hours, due to chemical burns and potential perforation of the esophagus.
- If you think batteries might have been swallowed or placed inside any part of the body, seek immediate medical attention.
- Don't heat, recharge, or bend the battery.
- Examine devices and make sure the battery compartment is correctly fastened, e.g., that the screw or other mechanical fastener is tightened. Do not use the product if the compartment is not secure.
- Used batteries need to be disposed of immediately and safely. Empty batteries can still cause harm.
- Tell others about the risk associated with batteries and how to keep their children safe.

Certificates



This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions:

- (1) This device may not cause harmful interference, and
- (2) this device must accept any interference received, including interference that may cause undesired operation.

CAUTION TO USERS

Changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment.

FCC rules apply to the following products: VUSION 1.5 (EDB1-0150-A); VUSION 1.6 (EDB1-0160-A); VUSION 2.1 (EDB1-0210-A); VUSION 2.1 WP (EWB1-0210-A); VUSION 2.2 (EDB1-0220-A, EDB1-0220-B); VUSION 2.6 (EDB1-0260-A); VUSION 4.2 WP (EWB1-0420-A); VUSION 7.4 (EDB1-0740-A)



This device contains licence-exempt transmitter(s)/receiver(s) that comply with Innovation, Science and Economic Development Canada's licence-exempt RSS(s). Operation is subject to the following two conditions:

- (1) This device may not cause interference.

(2) This device must accept any interference, including interference that may cause undesired operation of the device.

L'émetteur/récepteur exempt de licence contenu dans le présent appareil est conforme aux CNR d'Innovation, Sciences et Développement économique Canada applicables aux appareils radio exempts de licence. L'exploitation est autorisée aux deux conditions suivantes:

- 1) L'appareil ne doit pas produire de brouillage;
- 2) L'appareil doit accepter tout brouillage radioélectrique subi, même si le brouillage est susceptible d'en compromettre le fonctionnement.

IC standards apply to the following products: VUSION 1.5 (EDB1-0150-A); VUSION 1.6 (EDB1-0160-A); VUSION 2.1 (EDB1-0210-A); VUSION 2.1 WP (EWB1-0210-A); VUSION 2.2 (EDB1-0220-A, EDB1-0220-B); VUSION 2.6 (EDB1-0260-A); VUSION 4.2 WP (EWB1-0420-A); VUSION 7.4 (EDB1-0740-A)