APPENDIX C: SAR TISSUE SPECIFICATIONS

Measurement Procedure for Tissue verification:

- 1) The network analyzer and probe system was configured and calibrated.
- 2) The probe was immersed in the tissue. The tissue was placed in a nonmetallic container. Trapped air bubbles beneath the flange were minimized by placing the probe at a slight angle.
- 3) The complex admittance with respect to the probe aperture was measured
- 4) The complex relative permittivity ϵ can be calculated from the below equation (Pournaropoulos and Misra):

$$Y = \frac{j2\omega\varepsilon_{r}\varepsilon_{0}}{\left[\ln(b/a)\right]^{2}} \int_{a}^{b} \int_{a}^{b} \int_{0}^{\pi} \cos\phi' \frac{\exp\left[-j\omega r(\mu_{0}\varepsilon_{r}\varepsilon_{0})^{1/2}\right]}{r} d\phi' d\rho' d\rho$$

where Y is the admittance of the probe in contact with the sample, the primed and unprimed coordinates refer to source and observation points, respectively, $r^2 = \rho^2 + \rho'^2 - 2\rho\rho'\cos\phi'$, ω is the angular frequency, and $j = \sqrt{-1}$.

3 Composition / Information on ingredients

3.2 Mixture:

Description: Aqueous solution with surfactants and inhibitors

Decidiable, of flazardous components.					
CAS: 107-21-1	Ethanediol	>1.0-4.9%			
EINECS: 203-473-3	STOT RE 2, H373;				
Reg.nr.: 01-2119456816-28-0000	Acute Tox. 4, H302				
CAS: 68608-26-4	Sodium petroleum sulfonate	< 2.9%			
EINECS: 271-781-5	Eye Irrit. 2, H319				
Reg.nr.: 01-2119527859-22-0000					
CAS: 107-41-5	Hexylene Glycol / 2-Methyl-pentane-2,4-diol	< 2.9%			
EINECS: 203-489-0	Skin Irrit. 2, H315; Eye Irrit. 2, H319				
Reg.nr.: 01-2119539582-35-0000					
CAS: 68920-66-1	Alkoxylated alcohol, > C ₁₆	< 2.0%			
NLP: 500-236-9	Aquatic Chronic 2, H411;				
Reg.nr.: 01-2119489407-26-0000	Skin Irrit. 2, H315; Eye Irrit. 2, H319				

Additional information:

For the wording of the listed risk phrases refer to section 16.

Not mentioned CAS-, EINECS- or registration numbers are to be regarded as Proprietary/Confidential. The specific chemical identity and/or exact percentage concentration of proprietary components is withheld as a trade secret.

Figure C-1

Note: Liquid recipes are proprietary SPEAG. Since the composition is approximate to the actual liquids utilized, the manufacturer tissue-equivalent liquid data sheets are provided below.

FCC ID A3LSMA528B	SAR EVALUATION REPORT	SAMSUNG	Approved by: Quality Manager
Test Dates:	DUT Type:		APPENDIX C:
07/04/2021 - 07/25/2021	Portable Handset		Page 1 of 3

Zeughausstrasse 43, 8004 Zurich, Switzerland Phone +41 44 245 9700, Fax +41 44 245 9779 info@speag.com, http://www.speag.com

Measurement Certificate / Material Test

Item Name	Body Tissue Simulating Liquid (MBBL600-6000V6)	
Product No.	SL AAM U16 BC (Batch: 200803-1)	
Manufacturer	SPEAG	

Measurement Method

TSL dielectric parameters measured using calibrated DAK probe.

Target Parameters

Target parameters as defined in the KDB 865664 compliance standard.

Test Condition

Ambient Condition 22°C; 30% humidity
TSL Temperature 22°C

6-Aug-20 Operator

Additional Information
TSL Density
TSL Heat-capacity

	Measu	red	1/2 18	Targe	t	Diff.to Targ	get [%]	15.0						not see	-
[MHz]	e'	0"	sigma	eps	sigma	∆-eps	∆-sigma	10.0		17 16					
600	56.3	26.8	0.89	56.1	0.95	0.3	-6.3	%							
750	55.8	22.6	0.94	55.5	0.96	0.5	-2.1	2.0 0.0 0.0		_					
800	55.7	21.6	0.96	55.3	0.97	0.7	-1.0	E 0.0				NEW YEAR	1200		-
825	55.7	21.1	0.97	55.2	0.98	8.0	-1.0		1231						
835	55.7	20.9	0.98	55.1	0.99	1.0	-0.5	e -10.0	1397			Market II.		80 9	
850	55.6	20.7	0.98	55.2	0.99	0.8	-1.0	-15.0	500	1500	2500	3500	4500	550	n
900	55.5	19.9	1.00	55.0	1.05	0.9	-4.8		300	1500	Freque	ncy MHz	4500	550	~
1400	54.7	15.9	1.24	54.1	1.28	1.1	-3.1	15.0	1		and their			3000	(2.34)
1450	54.6	15.8	1.27	54.0	1.30	1.1	-2.3	10.0	100		Party			200	
1600	54.4	15.3	1.36	53.8	1.39	1.1	-2.2	» > 5.0							-
1625	54.4	15.3	1.38	53.8	1.41	1.2	-2.1	Conductivity 0.0 2-2-	1	1	1			/	
1640	54.4	15.2	1.39	53.7	1.42	1.3	-2.1	onpr	Λ	1	1		/		
1650	54.3	15.2	1.39	53.7	1.43	1.1	-2.8	§ -5.0	1-			_			
1700	54.2	15.1	1.43	53.6	1.46	1.2	-2.1	à-10.0	3300			9864	1	DI N	1
1750	54.2	15.0	1.46	53.4	1.49	1.4	-2.0	-15.0	500	1500	2500	3500	4500	550	20
1800	54.1	14.9	1.50	53.3	1.52	1.5	-1.3		300	1000	Freque	3500 ncy MHz	4000	550	~
1810	54.1	14.9	1.51	53.3	1.52	1.5	-0.7	3500	51.4	16.0	3.11	51.3	3.31	0.2	-
1825	54.1	14.9	1.52	53.3	1.52	1.5	0.0	3700	51.1	16.2	3.34	51.1	3.55	0.1	4
1850	54.0	14.9	1.53	53.3	1.52	1.3	0.7	5200	48.3	18.7	5.42	49.0	5.30	-1.5	- 3
	54.0	14.8	1.57	53.3	1.52	1.3	3.3	5250	48.2	18.8	5.50	49.0	5.36	-1.6	8
1900											100000				
1900 1950	53.9	14.8	1.60	53.3	1.52	1.1	5.3	5300	48.1	18.9	5.57	48.9	5.42	-1.7	3
1950		14.8 14.8	1.60	53.3 53.3	1.52	1.1	5.3 7.9	5300 5500	48.1 47.7	18.9 19.2	5.57 5.86	48.9 48.6	5.42 5.65	-1.7	
1950 2000	53.9	10000	的接受到	10000	100000		100000		Microsoph.	100000	30.57				
1950 2000 2050	53.9 53.8	14.8	1.64	53.3	1.52	0.9	7.9	5500	47.7	19.2	5.86	48.6	5.65	-2.0	
1950 2000 2050 2100	53.9 53.8 53.8	14.8 14.7	1.64 1.68	53.3 53.2	1.52 1.57	0.9	7.9 7.0	5500 5600	47.7 47.5	19.2 19.3	5.86 6.01	48.6 48.5	5.65 5.77	-2.0 -2.1	
	53.9 53.8 53.8 53.7	14.8 14.7 14.7	1.64 1.68 1.72	53.3 53.2 53.2	1.52 1.57 1.62	0.9 1.1 1.0	7.9 7.0 6.2	5500 5600 5700	47.7 47.5 47.3	19.2 19.3 19.4	5.86 6.01 6.16	48.6 48.5 48.3	5.65 5.77 5.88	-2.0 -2.1 -2.3	
1950 2000 2050 2100 2150 2200	53.9 53.8 53.8 53.7 53.7	14.8 14.7 14.7 14.7	1.64 1.68 1.72 1.76	53.3 53.2 53.2 53.1	1.52 1.57 1.62 1.66	0.9 1.1 1.0 1.1	7.9 7.0 6.2 6.0	5500 5600 5700 5800	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	
1950 2000 2050 2100 2150 2200 2250	53.9 53.8 53.8 53.7 53.7 53.6	14.8 14.7 14.7 14.7 14.7	1.64 1.68 1.72 1.76 1.80	53.3 53.2 53.2 53.1 53.0	1.52 1.57 1.62 1.66 1.71	0.9 1.1 1.0 1.1 1.1	7.9 7.0 6.2 6.0 5.3	5500 5600 5700 5800 6000	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	
1950 2000 2050 2100 2150 2200 2250 2300	53.9 53.8 53.8 53.7 53.7 53.6 53.5	14.8 14.7 14.7 14.7 14.7 14.8	1.64 1.68 1.72 1.76 1.80 1.85	53.3 53.2 53.2 53.1 53.0 53.0	1.52 1.57 1.62 1.66 1.71 1.76	0.9 1.1 1.0 1.1 1.1	7.9 7.0 6.2 6.0 5.3 5.1	5500 5600 5700 5800 6000 6500	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	
1950 2000 2050 2100 2150	53.9 53.8 53.7 53.7 53.6 53.5 53.5	14.8 14.7 14.7 14.7 14.7 14.8 14.8	1.64 1.68 1.72 1.76 1.80 1.85 1.89	53.3 53.2 53.2 53.1 53.0 53.0 52.9	1.52 1.57 1.62 1.66 1.71 1.76 1.81	0.9 1.1 1.0 1.1 1.1 1.0 1.1	7.9 7.0 6.2 6.0 5.3 5.1 4.4	5500 5600 5700 5800 6000 6500 7000	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	
1950 2000 2050 2100 2150 2200 2250 2300 2350 2400	53.9 53.8 53.8 53.7 53.7 53.6 53.5 53.5	14.8 14.7 14.7 14.7 14.7 14.8 14.8	1.64 1.68 1.72 1.76 1.80 1.85 1.89	53.3 53.2 53.2 53.1 53.0 53.0 52.9 52.8	1.52 1.57 1.62 1.66 1.71 1.76 1.81 1.85	0.9 1.1 1.0 1.1 1.1 1.0 1.1	7.9 7.0 6.2 6.0 5.3 5.1 4.4	5500 5600 5700 5800 6000 6500 7000 7500	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	
1950 2000 2050 2100 2150 2250 2250 2350 2400 2450	53.9 53.8 53.7 53.7 53.6 53.5 53.5 53.4 53.3	14.8 14.7 14.7 14.7 14.7 14.8 14.8 14.8	1.64 1.68 1.72 1.76 1.80 1.85 1.89 1.94	53.3 53.2 53.2 53.1 53.0 53.0 52.9 52.8	1.52 1.57 1.62 1.66 1.71 1.76 1.81 1.85	0.9 1.1 1.0 1.1 1.1 1.0 1.1 1.1	7.9 7.0 6.2 6.0 5.3 5.1 4.4 4.9	5500 5600 5700 5800 6000 6500 7000 7500 8000	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	
1950 2000 2050 2100 2150 2200 2250 2300 2350	53.9 53.8 53.7 53.7 53.6 53.5 53.5 53.4 53.3	14.8 14.7 14.7 14.7 14.7 14.8 14.8 14.8 14.8	1.64 1.68 1.72 1.76 1.80 1.85 1.89 1.94 1.98 2.03	53.3 53.2 53.2 53.1 53.0 53.0 52.9 52.8 52.8 52.7	1.52 1.57 1.62 1.66 1.71 1.76 1.81 1.85 1.90	0.9 1.1 1.0 1.1 1.0 1.1 1.0 1.1 1.0 1.1 1.1	7.9 7.0 6.2 6.0 5.3 5.1 4.4 4.9 4.2	5500 5600 5700 5800 6000 6500 7000 7500 8000 8500	47.7 47.5 47.3 47.0	19.2 19.3 19.4 19.6	5.86 6.01 6.16 6.32	48.6 48.5 48.3 48.2	5.65 5.77 5.88 6.00	-2.0 -2.1 -2.3 -2.4	

Figure C-2 600 - 5800 MHz Body Tissue Equivalent Matter

500 ID ACL OMA 500D	<i>©</i> Λ PCTEST°	CAR EVALUATION REPORT	SAMSUNG	Approved by:	
FCC ID A3LSMA528B	Proud to be part of @ element	SAR EVALUATION REPORT	SAMSUNG	Quality Manager	
Test Dates:	DUT Type:			APPENDIX C:	
07/04/2021 - 07/25/2021	Portable Handset			Page 2 of 3	

-5.3

-1.0

-0.9

-0.7

-0.1

0.2

0.4

0.7

1.2

1.6

2.0

-4.7 2.1

Zeughausstrasse 43, 8004 Zurich, Switzerland Phone +41 44 245 9700, Fax +41 44 245 9779 info@speag.com, http://www.speag.com

Measurement Certificate / Material Test

Item Name Head Tissue Simulating Liquid (HBBL600-10000V6)

Product No. SL AAH U16 BC (Batch: 200805-4)

Manufacturer SPEAG

Measurement Method

TSL dielectric parameters measured using calibrated DAK probe.

Target Parameters

Target parameters as defined in the IEEE 1528 and IEC 62209 compliance standards.

Test Condition

Ambient Condition 22°C; 30% humidity

TSL Temperature 22°C
Test Date 6-Aug-20
Operator CL

Additional Information

TSL Density

2350 41.3 13.6 1.78 39.4 1.71

2400 41.2 13.6 1.82 39.3 1.76

2500 41.1 13.6 1.89 39.1 1.85

2550 41.0 13.7 1.94 39.1 1.91

40.9

1.85 39.2 1.80

39.0

TSL Heat-capacity

Diff.to Target [%] f [MHz] e' e" sigma eps sigma ∆-eps ∆-sigma 10.0 25.7 42.7 0.88 4.6 600 0.86 -2.5 % 5.0 0.0 5.0 800 20.7 0.92 41.7 0.90 5.6 2.5 825 43.9 20.3 0.93 41.6 0.91 5.6 2.6 10.0 2-15.0 835 43.9 20.1 0.94 41.5 0.91 5.7 3.1 41.5 0.92 850 19.9 0.94 5.5 2.6 43.8 500 1500 2500 3500 4500 5500 6500 7500 8500 9500 Frequency MHz 900 19.1 41.5 0.97 5.3 -1.0 1.18 40.6 0.0 1450 42.6 14.9 1.20 40.5 1.20 5.2 0.0 10.0 1600 42.4 14.4 1.28 40.3 1.28 5.2 -0.3 5.0 14.4 40.3 1.30 1625 42.4 1.30 5.3 0.1 \$ 0.0 14.3 40.3 1.31 5.0 5.0 10.0 1640 0.3 42.4 1.31 5.3 42.3 14.3 1.31 40.2 1.31 5.1 -0.2 1700 42.2 14.2 1.34 40.2 1.34 5.1 -0.2 å15.0 1750 42.2 14.1 1.37 40.1 1.37 5.3 -0.1 500 1500 2500 3500 4500 5500 6500 7500 8500 9500 1800 42.1 14.0 1.40 40.0 1.40 5.3 0.0 equency MH 1810 40.0 1.40 42.1 14.0 1.41 5.3 0.7 3500 2.77 37.9 13.9 1.42 40.0 1.40 5.3 1.4 3700 39.0 14.3 37.7 3.12 3.5 1825 42.1 2.95 40.0 5.0 2.1 4.66 1900 41.9 13.8 1.46 40.0 1.40 4.7 4.3 5250 16.0 35.9 4.71 1.2 1950 41.9 13.8 1.49 40.0 1.40 4.7 6.4 5300 36.3 16.0 4.72 35.9 4.76 1.1 40.0 1.40 2000 41.8 13.7 1.53 4.5 9.3 5500 35.9 16.2 4.96 35.6 4.96 0.7 1.56 39.9 1.44 4.5 5600 35.5 0.5 2050 41.7 13.7 8.0 35.7 16.3 5.07 5.07 2100 41.7 13.7 1.60 39.8 1.49 4.7 7.5 5700 35.5 16.4 35.4 5.17 0.3 5.19 2150 13.6 1.63 39.7 1.53 5800 35.4 16.5 35.3 5.27 0.1 2200 41.5 13.6 1.67 39.6 1.58 4.7 5.8 6000 35.0 16.6 5.54 35.1 5.48 -0.2 2250 41.5 13.6 1.70 39.6 1.62 4.9 4.8 6500 34.1 17.1 6.17 34.5 6.07 -1.1 2300 41.4 13.6 1.74 39.5 1.67 4.9 4.4 7000 33.2 17.4 6.78 33.9 6.65 -2.0

4.9

4.9

5.0

4.9

4.0

3.7

2.8

1.9

1.6

0.8

Figure C-3
600 – 5800 MHz Head Tissue Equivalent Matter

7500 32.3

8000 31.5 18.0 8.01 32.7 7.84 -3.8 2.2

8500

9000 29.8 18.4 9.24 31.5 9.08 -5.6 1.8

9500 29.0 18.6 9.84 31.0 9.71 -6.5 1.3

17.7

7.40 33.3 7.24 -2.9 2.2

32.1

FCC ID A3LSMA528B	Proxi to be part of @ element	SAR EVALUATION REPORT	SAMSUNG	Approved by: Quality Manager
Test Dates:	DUT Type:			APPENDIX C:
07/04/2021 - 07/25/2021	Portable Handset			Page 3 of 3