

## APPENDIX E: SAR TISSUE SPECIFICATIONS

Measurement Procedure for Tissue verification:

- 1) The network analyzer and probe system was configured and calibrated.
- 2) The probe was immersed in the tissue. The tissue was placed in a nonmetallic container. Trapped air bubbles beneath the flange were minimized by placing the probe at a slight angle.
- 3) The complex admittance with respect to the probe aperture was measured
- 4) The complex relative permittivity  $\epsilon'$  can be calculated from the below equation (Pournaropoulos and Misra):

$$Y = \frac{j2\omega\epsilon_r\epsilon_0}{[\ln(b/a)]^2} \int_a^b \int_a^b \int_0^\pi \cos\phi' \frac{\exp[-j\omega r(\mu_0\epsilon_r'\epsilon_0)^{1/2}]}{r} d\phi' d\rho' d\rho$$

where Y is the admittance of the probe in contact with the sample, the primed and unprimed coordinates refer to source and observation points, respectively,  $r^2 = \rho^2 + \rho'^2 - 2\rho\rho' \cos\phi'$ ,  $\omega$  is the angular frequency, and  $j = \sqrt{-1}$ .

### 3 Composition / Information on ingredients

#### 3.2 Mixtures

**Description:** Aqueous solution with surfactants and inhibitors

**Declarable, or hazardous components:**

|  |   |           |
|--|---|-----------|
| CAS: 107-21-1<br>EINECS: 203-473-3<br>Reg.nr.: 01-2119456816-28-0000   | <b>Ethanediol</b><br>STOT RE 2, H373;<br>Acute Tox. 4, H302   | >1.0-4.9% |
| CAS: 68608-26-4<br>EINECS: 271-781-5<br>Reg.nr.: 01-2119527859-22-0000 | <b>Sodium petroleum sulfonate</b><br>Eye Irrit. 2, H319   | < 2.9%    |
| CAS: 107-41-5<br>EINECS: 203-489-0<br>Reg.nr.: 01-2119539582-35-0000   | <b>Hexylene Glycol / 2-Methyl-pentane-2,4-diol</b><br>Skin Irrit. 2, H315; Eye Irrit. 2, H319                         | < 2.9%    |
| CAS: 68920-66-1<br>NLP: 500-236-9<br>Reg.nr.: 01-2119489407-26-0000    | <b>Alkoxyated alcohol, &gt; C<sub>16</sub></b><br>Aquatic Chronic 2, H411;<br>Skin Irrit. 2, H315; Eye Irrit. 2, H319 | < 2.0%    |

**Additional information:**




For the wording of the listed risk phrases refer to section 16.

Not mentioned CAS-, EINECS- or registration numbers are to be regarded as Proprietary/Confidential.

The specific chemical identity and/or exact percentage concentration of proprietary components is withheld as a trade secret.

**Figure E-1**

Note: Liquid recipes are proprietary SPEAG. Since the composition is approximate to the actual liquids utilized, the manufacturer tissue-equivalent liquid data sheets are provided below.

|  |  |                                      |   |                                   |
|--|--|--------------------------------------|---|-----------------------------------|
| FCC ID: A3LSMS908E                     |  <b>PCTEST</b><br>Proud to be part of  | WIFI 6 GHZ RF EXPOSURE<br>EVALUATION |  | Approved by:<br>Technical Manager |
| Test Dates:<br>11/08/2021 – 12/08/2021 | DUT Type:<br>Portable Handset  | APPENDIX E:<br>Page 1 of 2           |   |                                   |

**Measurement Certificate / Material Test**

|              |   |
|--------------|---|
| Item Name    | Head Tissue Simulating Liquid (HBBL600-10000V6) |
| Product No.  | SL AAH U16 BC (Batch: 200805-4)                 |
| Manufacturer | SPEAG   |

**Measurement Method**

TSL dielectric parameters measured using calibrated DAK probe.

**Target Parameters**

Target parameters as defined in the IEEE 1528 and IEC 62209 compliance standards.

**Test Condition**



Ambient Condition 22°C ; 30% humidity  
 TSL Temperature 22°C  
 Test Date 6-Aug-20  
 Operator CL

**Additional Information**

TSL Density  
 TSL Heat-capacity

**Results**

| f [MHz] | Measured |      |       | Target |       | Diff.to Target [%] |         |
|---------|----------|------|-------|--------|-------|--------------------|---------|
|         | e'       | e''  | sigma | eps    | sigma | Δ-eps              | Δ-sigma |
| 600     | 44.7     | 25.7 | 0.86  | 42.7   | 0.88  | 4.6                | -2.5    |
| 750     | 44.1     | 21.7 | 0.90  | 41.9   | 0.89  | 5.1                | 0.7     |
| 800     | 44.0     | 20.7 | 0.92  | 41.7   | 0.90  | 5.6                | 2.5     |
| 825     | 43.9     | 20.3 | 0.93  | 41.6   | 0.91  | 5.6                | 2.6     |
| 835     | 43.9     | 20.1 | 0.94  | 41.5   | 0.91  | 5.7                | 3.1     |
| 850     | 43.8     | 19.9 | 0.94  | 41.5   | 0.92  | 5.5                | 2.6     |
| 900     | 43.7     | 19.1 | 0.96  | 41.5   | 0.97  | 5.3                | -1.0    |
| 1400    | 42.7     | 15.1 | 1.18  | 40.6   | 1.18  | 5.2                | 0.0     |
| 1450    | 42.6     | 14.9 | 1.20  | 40.5   | 1.20  | 5.2                | 0.0     |
| 1600    | 42.4     | 14.4 | 1.28  | 40.3   | 1.28  | 5.2                | -0.3    |
| 1625    | 42.4     | 14.4 | 1.30  | 40.3   | 1.30  | 5.3                | 0.1     |
| 1640    | 42.4     | 14.3 | 1.31  | 40.3   | 1.31  | 5.3                | 0.3     |
| 1650    | 42.3     | 14.3 | 1.31  | 40.2   | 1.31  | 5.1                | -0.2    |
| 1700    | 42.2     | 14.2 | 1.34  | 40.2   | 1.34  | 5.1                | -0.2    |
| 1750    | 42.2     | 14.1 | 1.37  | 40.1   | 1.37  | 5.3                | -0.1    |
| 1800    | 42.1     | 14.0 | 1.40  | 40.0   | 1.40  | 5.3                | 0.0     |
| 1810    | 42.1     | 14.0 | 1.41  | 40.0   | 1.40  | 5.3                | 0.7     |
| 1825    | 42.1     | 13.9 | 1.42  | 40.0   | 1.40  | 5.3                | 1.4     |
| 1850    | 42.0     | 13.9 | 1.43  | 40.0   | 1.40  | 5.0                | 2.1     |
| 1900    | 41.9     | 13.8 | 1.46  | 40.0   | 1.40  | 4.7                | 4.3     |
| 1950    | 41.9     | 13.8 | 1.49  | 40.0   | 1.40  | 4.7                | 6.4     |
| 2000    | 41.8     | 13.7 | 1.53  | 40.0   | 1.40  | 4.5                | 9.3     |
| 2050    | 41.7     | 13.7 | 1.56  | 39.9   | 1.44  | 4.5                | 8.0     |
| 2100    | 41.7     | 13.7 | 1.60  | 39.8   | 1.49  | 4.7                | 7.5     |
| 2150    | 41.6     | 13.6 | 1.63  | 39.7   | 1.53  | 4.7                | 6.3     |
| 2200    | 41.5     | 13.6 | 1.67  | 39.6   | 1.58  | 4.7                | 5.8     |
| 2250    | 41.5     | 13.6 | 1.70  | 39.6   | 1.62  | 4.9                | 4.8     |
| 2300    | 41.4     | 13.6 | 1.74  | 39.5   | 1.67  | 4.9                | 4.4     |
| 2350    | 41.3     | 13.6 | 1.78  | 39.4   | 1.71  | 4.9                | 4.0     |
| 2400    | 41.2     | 13.6 | 1.82  | 39.3   | 1.76  | 4.9                | 3.7     |
| 2450    | 41.2     | 13.6 | 1.85  | 39.2   | 1.80  | 5.1                | 2.8     |
| 2500    | 41.1     | 13.6 | 1.89  | 39.1   | 1.85  | 5.0                | 1.9     |
| 2550    | 41.0     | 13.7 | 1.94  | 39.1   | 1.91  | 4.9                | 1.6     |
| 2600    | 40.9     | 13.7 | 1.98  | 39.0   | 1.96  | 4.8                | 0.8     |



|       |      |      |       |      |       |      |      |
|-------|------|------|-------|------|-------|------|------|
| 3500  | 39.4 | 14.2 | 2.77  | 37.9 | 2.91  | 3.7  | -5.1 |
| 3700  | 39.0 | 14.3 | 2.95  | 37.7 | 3.12  | 3.5  | -5.3 |
| 5200  | 36.4 | 15.9 | 4.61  | 36.0 | 4.66  | 1.3  | -1.0 |
| 5250  | 36.4 | 16.0 | 4.67  | 35.9 | 4.71  | 1.2  | -0.9 |
| 5300  | 36.3 | 16.0 | 4.72  | 35.9 | 4.76  | 1.1  | -0.7 |
| 5500  | 35.9 | 16.2 | 4.96  | 35.6 | 4.96  | 0.7  | -0.1 |
| 5600  | 35.7 | 16.3 | 5.07  | 35.5 | 5.07  | 0.5  | 0.2  |
| 5700  | 35.5 | 16.4 | 5.19  | 35.4 | 5.17  | 0.3  | 0.4  |
| 5800  | 35.4 | 16.5 | 5.31  | 35.3 | 5.27  | 0.1  | 0.7  |
| 6000  | 35.0 | 16.6 | 5.54  | 35.1 | 5.48  | -0.2 | 1.2  |
| 6500  | 34.1 | 17.1 | 6.17  | 34.5 | 6.07  | -1.1 | 1.6  |
| 7000  | 33.2 | 17.4 | 6.78  | 33.9 | 6.65  | -2.0 | 2.0  |
| 7500  | 32.3 | 17.7 | 7.40  | 33.3 | 7.24  | -2.9 | 2.2  |
| 8000  | 31.5 | 18.0 | 8.01  | 32.7 | 7.84  | -3.8 | 2.2  |
| 8500  | 30.6 | 18.2 | 8.63  | 32.1 | 8.45  | -4.7 | 2.1  |
| 9000  | 29.8 | 18.4 | 9.24  | 31.5 | 9.08  | -5.6 | 1.8  |
| 9500  | 29.0 | 18.6 | 9.84  | 31.0 | 9.71  | -6.5 | 1.3  |
| 10000 | 28.1 | 18.8 | 10.44 | 30.4 | 10.36 | -7.4 | 0.8  |

**Figure E-2**  
**600 – 10000 MHz Head Tissue Equivalent Matter**

|  |                                       |                                      |  |                                   |
|--|---------------------------------------|--------------------------------------|--|-----------------------------------|
| FCC ID: A3LSMS908E                     | PCTEST<br>Proud to be part of element | WIFI 6 GHZ RF EXPOSURE<br>EVALUATION |  | Approved by:<br>Technical Manager |
| Test Dates:<br>11/08/2021 – 12/08/2021 | DUT Type:<br>Portable Handset         |                                      |  | APPENDIX E:<br>Page 2 of 2        |