

FIRST USED ON:
S790S2/T2

PART NO:
40A155-XXXX

REVISION

VERSION A 99/欄7竣10

興道肇

ADG COLOR MONITOR

Model No. : 7Glr
Power Rating: 100-240V ~ 50/60Hz 2.5A

AOC International (Europe) GmbH
Lahnstrasse 86a
D-12055 Berlin
Germany

Geprüft nach Tested Acc. to
MPR II: MPR 1990:8/1990:10

Made in China
40A2026-615-1A









FCC ID: ARSCM7950

This device complies with Part 15 of the FCC rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

This Class B digital apparatus meets all requirements of the Canadian Interference - Causing Equipment Regulations.
Cet appareil numérique de la classe B respecte toutes les exigences du Règlement sur le matériel brouilleur du Canada.

THIS DEVICE COMPLIES WITH FDA RADIATION PERFORMANCE STANDARDS, 21 CFR SUBCHAPTER J.

Die in diesem Gerät entstehende Röntgenstrahlung ist ausreichend abgeschirmt
Beschleunigungsspannung: max. 28.5KV
Cathode Ray Tube intrinsically safe according to appendix III Röntgenverordnung
Eigenschere Kathodenstrahlröhre nach Anlage III Röntgenverordnung

LRC0041

NOTE:

1. 芎芘喉酸獾掛洋〔
2. 喜渡鼠船 0.5mm, 血筭R 裏0.2mm 〔
3. 第塞L PET 湍祥補掖蝶 〔
4. 菁伎L 宵伎準謠酸乙 芎芘跣极略窪伎 〔
5. 芎芘祥褫衤祛蘋摯跨伎 祥歛張祥謎聊砬 〔
6. 笛晚荆狂塗 〔

TOP VICTORY ELECTRONICS

CHECKED BY:

華施 : 腦標卽腦 李咪粹織嫩莎
 莫趕 : (0591)5285555. 5285559
 換凌 : (0591)5285447
 就話 : 350301

夢豎莫趙(腦標)卽發鼠伺