


| REVISIONS |        |      |          |
|-----------|--------|------|----------|
| REV       | CO/PRN | DATE | APPROVED |
| -         | 161664 | 8/99 | JN       |
| A         | 161215 | 9/99 | JN       |



THIS DRAWING IS NOT COMPLETE WITHOUT  
PARTS LIST 069-01033-XXXX.

**AUTHORIZED PRINT**

|                                                                                                 |                                                       |                |                   |                                   |                       |         |
|-------------------------------------------------------------------------------------------------|-------------------------------------------------------|----------------|-------------------|-----------------------------------|-----------------------|---------|
| ---                                                                                             | UNIT                                                  | KX165A         | 1000-             |                                   |                       |         |
| NEXT Assy                                                                                       |                                                       |                |                   | PART NO                           | DESCRIPTION           | FIND NO |
| <p>TOL UNLESS NOTED<br/>         XX ±0.02<br/>         XXX ±0.010<br/>         ANGLES ±0.5°</p> |                                                       |                |                   |                                   |                       |         |
| MATERIAL                                                                                        |                                                       | DRN NERHAM     |                   | NAME                              | KX165A FINAL ASSEMBLY |         |
|                                                                                                 |                                                       | DATE 26-AUG-99 |                   |                                   |                       |         |
| FINISH                                                                                          | PROLE CULUMBER<br>300-09095 5010 - 099<br>500PCL, LGT | SCALE<br>NONE  | PIN RANGE<br>NONE | DOCUMENT NUMBER<br>300-09095-0010 | SHT 1<br>OF 2         |         |

**AlliedSignal Proprietary**

This document and all information and expression contained herein are the property of AlliedSignal Inc. and are lent in confidence, and may not, in whole or, in part, be used, duplicated or disclosed for any purpose without prior written permission of AlliedSignal.

This document is an unpublished work.  
Copyright 1998 AlliedSignal Inc. All rights reserved.

NOTES

1. CUT ITEM 12 TO INDICATED LENGTHS BEFORE INSTALLING.
2. CONNECT GLIDESLOPE CABLE (FROM ITEM 2) TO INDICATED LOCATION ON MAIN BOARD (PART OF ITEM 1). DRESS CABLE SO THAT IT WILL NOT BE PINCHED WHEN UNIT IS ASSEMBLED.
3. PREFORM ITEM 26 BEFORE INSTALLING. SEE DETAIL A.
4. INSTALL ITEMS 25 AND 26 USING INDICATED SCREWS.
5. APPLY THERMAL JOINT COMPOUND (ITEM 24) TO INDICATED SURFACE BEFORE INSTALLING ITEM 2.
6. LIQUID STAKE ALL FASTENERS PER SPECIFICATION 001-01080-0000.
7. APPLY SOFTWARE IDENTIFICATION TAG, 057-05287-XXXX (FROM 206-00379) AS SHOWN.
8. UNIT IS SHIPPED IN MOUNTING RACK, ITEM 6.

DETAIL A

