Head Tissue Simulating Liquids

Application	Specific absorption rate acc	ording to standards (e.g., IEC 62209	-x, IEEE 1528)					
Packaging	Plastic container of 10 liters with nozzle							
Life Time	Life time and stability of the simulating liquid	e liquid depend on usage, storage, a	nd handling of tissue					
Options	Tissue simulating liquids for frequencies outside the below listed ranges are available upon request (please contact info@speag.swiss)							
Head Tissue	Parameters according to IEEE 1528 / IEC 62209-1/ IEC 62209-2 / FCC KDB 865664							
Narrow- Band Solutions (±5% Tolerance) Broad- Band Solutions	Product HSL300V2 HSL450V2 HSL750V2 HSL900V2 Product HBBL1350-1850V3	Test Frequency (MHz) 300 450 750 835, 900 Test Frequency (MHz) 1450 - 1800	Main Ingredients Water, Sugar Water, Sugar Water, Sugar Water, Sugar Water, Tween					
(±5% Tolerance)	HBBL1550-1950V3 HBBL1900-3800V3 HBBL3500-5800V5	1750 - 1850 1950 - 3000 3500 - 5800	Water, Tween Water, Tween Water, Oil					
Broad- Band Solutions (±10% Tolerance)	Product HBBL4-250V3 HBBL1350-1850V3 HBBL1550-1950V3 HBBL1900-3800V3 HBBL600-10000V6	Test Frequency (MHz) 4 - 250 1300 - 1850 1550 - 1950 1900 - 3800 600 - 10000	Main Ingredients Water, Tween Water, Tween Water, Tween Water, Tween Water, Oil					

Zeughausstrasse 43, 8004 Zurich, Switzerland Phone +41 44 245 9700, Fax +41 44 245 9779 info@speag.com, http://www.speag.com

Measurement Certificate / Material Test

Item Name Head Tissue Simulating Liquid (HBBL600-10000V6)

Product No. SL AAH U16 BD (Batch: 180208-1)

Manufacturer SPEAG

Measurement Method

TSL dielectric parameters measured using calibrated DAK probe.

Target Parameters

Target parameters as defined in the IEEE 1528 and IEC 62209 compliance standards.

Test Condition

Ambient Condition 22°C; 30% humidity

TSL Temperature 22°C Test Date 8-Feb-18

Operator WM


Additional Information


TSL Density

TSL Heat-capacity

Results

	Meas	ured	SEX	Targe	t	Diff.to Target [%]		
f [MHz]	0'	е"	sigma	eps	sigma	∆-eps	Δ-sigma	
800	44.1	20.3	0.90	41.7	0.90	5.8	0.3	
825	44.1	19.9	0.91	41.6	0.91	6.0	0.4	
835	44.1	19.7	0.92	41.5	0.91	6.1	0.9	
850	44.0	19.4	0.92	41.5	0.92	6.0	0.4	
900	43.9	18.7	0.94	41.5	0.97	5.8	-3.1	
1400	42.9	14.9	1.16	40.6	1.18	5.7	-1.6	
1450	42.8	14.7	1.18	40.5	1.20	5.7	-1.7	
1600	42.6	14.2	1.26	40.3	1.28	5.7	-1.9	
1625	42.6	14.1	1.28	40.3	1.30	5.8	-1.4	
1640	42.6	14.1	1.29	40.3	1.31	5.8	-1.2	
1650	42.5	14.1	1.29	40.2	1.31	5.6	-1.8	
1700	42.4	14.0	1.32	40.2	1.34	5.6	-1.6	
1750	42.3	13.9	1.35	40.1	1.37	5.5	-1.5	
1800	42.3	13.8	1.38	40.0	1.40	5.7	-1.4	
1810	42.3	13.8	1.39	40.0	1.40	5.7	-0.7	
1825	42.3	13.7	1.40	40.0	1.40	5.7	0.0	
1850	42.2	13.7	1.41	40.0	1.40	5.5	0.7	
1900	42.1	13.6	1.44	40.0	1.40	5.3	2.9	
1950	42.0	13.6	1.47	40.0	1.40	5.0	5.0	
2000	42.0	13.5	1.51	40.0	1.40	5.0	7.9	
2050	41.9	13.5	1.54	39.9	1.44	5.0	6.6	
2100	41.8	13.5	1.57	39.8	1.49	5.0	5.4	
2150	41.8	13.5	1.61	39.7	1.53	5.2	5.0	
2200	41.7	13.4	1.64	39.6	1.58	5.2	3.9	
2250	41.6	13.4	1.68	39.6	1.62	5.2	3.6	
2300	41.6	13.4	1.72	39.5	1.67	5.4	3.2	
2350	41.5	13.4	1.76	39.4	1.71	5.4	2.9	
2400	41.4	13.5	1.80	39.3	1.76	5.4	2.5	
2450	41.4	13.5	1.84	39.2	1.80	5.6	2.2	
2500	41.3	13.5	1.88	39.1	1.85	5.5	1.4	
2550	41.2	13.5	1.92	39.1	1.91	5.4	0.6	
2600	41.1	13.6	1.96	39.0	1.96	5.4	-0.2	
3500	39.6	14.1	2.75	37.9	2.91	4.3	-5.5	
3700	39.2	14.3	2.94	37.7	3.12	4.1	-5.7	





			Frequer	ncy MHz		5000	-
5200	36.7	15.9	4.61	36.0	4.66	1.9	-1.0
5250	36.6	16.0	4.67	35.9	4.71	1.8	-0.9
5300	36.5	16.0	4.72	35.9	4.76	1.7	-0.7
5500	36.1	16.2	4.96	35.6	4.96	1.3	-0.1
5600	35.9	16.3	5.08	35.5	5.07	1.1	0.2
5700	35.7	16.4	5.19	35.4	5.17	0.9	0.5
5800	35.6	16.5	5.31	35.3	5.27	0.8	0.8
6000	35.2	16.6	5.55	35.1	5.48	0.4	1.3
6500	34.3	17.1	6.18	34.5	6.07	-0.5	1.8
7000	33.4	17.5	6.81	33.9	6.65	-1.4	2.3
7500	32.5	17.8	7.43	33.3	7.24	-2.3	2.7
8000	31.7	18.1	8.06	32.7	7.84	-3.2	2.8
8500	30.8	18.4	8.68	32.1	8.45	-4.2	2.8
9000	30.0	18.6	9.31	31.5	9.08	-5.1	2.6
9500	29.1	18.8	9.93	31.0	9.71	-5.9	2.2
10000	28.3	19.0	10.55	30.4	10.36	-6.9	1.8

Zeughausstrasse 43, 8004 Zurich, Switzerland Phone +41 44 245 9700, Fax +41 44 245 9779 www.speag.swiss, info@speag.swiss

Measurement Certificate / Material Test

Head Tissue Simulating Liquid (HBBL4-250V3) Item Name

Product No. SL AAH 005 AD (Batch: 211221-1)

Manufacturer SPEAG

Measurement Method

TSL dielectric parameters measured using calibrated DAK probe.

Setup Validation

Validation results were within $\pm 2.5\%$ towards the target values of Methanol.

Target parameters as defined in the IEEE 1528 and IEC 62209 compliance standards.

Test Condition

Ambient Environment temperatur (22 ± 3)°C and humidity < 70%.

TSL Temperature 22°C Test Date 7-Jan-22 Operator JML

Additional Information

TSL Density 1.042 g/cm3 TSL Heat-capacity 3.574 kJ/(kg*K)

	Mea	sured	Tar	get		Diff.to Target [%			
f (MH	[2] e'	e' e" sigma			is sig				
5	53.7	-	-	_		75	-3.2	-4.9	_
10	53.7	511	10.414			75	-3.2	-4.9	
15	53.5	855.85				75	-3.4	-4.8	
20	53.3	642,50	17566	6337		- 1	-3.3	-4.7	
25	53.1	-	(35)	1238			-3.5	-4.6	
30	52.0					- 1	-3.9	-4.5	
35	52.7		1000	955		- 4	-4.1	-4.4	
40	52.5	89	1000	-		- 1	-4.2	-4.2	
45	52.3					- 1	-4.3	-4.1	
50	52.1	258.93	11000	250		- 1	-4.4	-4.0	
55	52.0	9	11/2				-4.5	-3.9	
60	51.8	216.52				1	-4.6	-3.8	
65	51.7	200.24	0.7	36		- 1	-4.6	-3.7	
70	51.6	188.31	0.7	1		- 11	-4.6		
75	51.5	174.24	0.7	10			-4.7	-3.6	
80	51.4	163.70	0.7	2.0		- 1		-3.4	
85	51.2	154.40	0.7	100		- 1	-4.7	-3.3	
90	51.1	148.15	0.7			- 11	-4.7	-3.1	
95	51.0	138,77	0.73			- 15	-4.7	-2,9	
100	50.9	132.14	0.74				-4.7	-2.8	
105	50.8	126.15	0.74				-4.7	-2.6	
110	50.7	120.71	(RESPON)	0		11	-4.7	-2.4	
115	50.6	115.75	0.74			110	-4.7	-2.2	
120	50.5		0.74				-4.7	-2.1	
125	50.4	111.21	0.74		0.76	- I	4.7	-1.0	
130	50.3	103.18	0.74		0.76	1	4.7	-1,7	
135	50.1	99,62	0.75		0.76		4.7	-1.5	
140	50.0	96.32	0.75	10.	0.76	4	4.7	-1.3	
145	49.9		0.75	52.5	0.76	1	4.7	-1.1	
150		93.24	0.75		0.76		4.7	-0.8	1
155	49.8	80,38	0.75	52.3	0.78		4.7	-0.6	1
	49.7	87.70	0.76	52.1	0.76	1	4.5	-0.8	1
150	49.6	85.20	0,76	51.8	0.77		4.2	-1,0	1
165	49.5	82.84	0.76	51.8	0.77	11	4.0	-1.2	1
70	48,4	80.83	U.76	51.4	U.//	-	3.7	-1.4	1
75	49,4	78.55	0.76	51.1	0.78	<	3.5	-1.6	1
80	49.3	76.58	0.77	50.9	0.78		3.2	-1.8	ı
85	49.2	74.72	0.77	50,7	0.78	4	3.0	-2.0	ı
90	49.1	72.96	0.77	50.4	0.79	-2	2.7	-2.2	ı
95	49.0	71.29	0.77	50.2	0.79	-2	2.4	-2,3	l
00	48.9	69.71	0.78	50.0	0.80	-2	2.1	-2.5	l
05	48,8	69.20	0.78	49.7	0.80	-1	.0	-2.7	ĺ
10	48.7	66.77	0.78	49.5	0.80	-1	.6	-2.8	l
15	48.6	65,41	0.78	49.3	0.81	-1	.3	-3.0	l
20	48.6	64.10	0.78	49.0	0.81	-1	.0	-3.2	
	48.5	62.86	0.79	48.8	0.81	-0	.7	-3.3	
	2200		0.000	48.6	0.82	-0	4	-3.5	L
30	48.4	61.67	0.79	70.0	V.La			-3.5	1
30	48.4 48.3	61.67 60.54	0.79	48.3	0.82	0.		-3.5 -3.6	
30	M-04-2031	- 1			- 11		0		

57.41

47.6 0.83

