

1.2. Operational Description

The EUT is Ergo 725 Laser used in household and office PC system. The number of the channels is 1 in 27.045MHz.

The device adopts FSK modulation and antenna type is soldered on PCB where U1 chip is a DC-DC converter providing 1.8V for reference.

The wireless optical mouse channel provides 256 ID-codes, and it automatically selects the ID # for the mouse. Only one wireless optical mouse can be set up at a time. But if you have additional wireless optical mouse sets in an area of 10 square meters, more interference will occur between the receiver and your mouse.

Test Mode	Mode 1: Transmitter
-----------	---------------------