




**Responsibility for Validation and Fitness-of-Use:**  
 Because Valmark Industries, Inc. has no control over the use or application of these parts, it is the sole responsibility of the OEM customer and/or its designated manufacturer to test all custom parts for fitness-of-use and validation of design prior to acceptance of production units. Valmark Industries provides expertise in the layout and consistent fabrication of high quality, reliable membrane switch, custom graphics and labeling products. Valmark and its employees do NOT purport to be experts in the end-use application of our customers, or the environments in which these products will be stored and/or used.

THIS PRINT MUST BE APPROVED AND RETURNED WITHIN 24 HOURS IN ORDER FOR THIS JOB TO PROCEED WITH PRODUCTION. ACCEPTANCE OF THE BELOW ART SAMPLE RELEASES VALMARK OF ANY GRAPHICS LIABILITY AFTER THE PRODUCTION RUN. (1) Valmark may, at its discretion unless otherwise noted, substitute any materials or BOM components with equivalent or similar materials and/or components based on control of cost or availability

Customer Supplied Prints			
	Part Number	Date	
Dimensional			
Graphics			
Modifications			
Rev.	ECO #	Description	Date

DETAILED DIMENSIONS ARE IN THE CUSTOMER SUPPLIED DRAWING



APPROVAL PRINT

RESUBMIT WITH CORRECTIONS

APPROVED WITH CORRECTIONS

OK AS IS

APPROVAL SIGNATURE \_\_\_\_\_ DATE \_\_\_\_\_

NOTES:	CONSTRUCTION:
1 LABEL PERIPHERY-keyline does not print	BASE MATERIAL .007" GE FR83-112
2 BACKGROUND: TRIMBLE MED. GREY NCS 5505-BO7G	ADHESIVE - FULL 3M 468
3 GRAPHICS: BLACK	
4 WHITE FOR OPACITY	

DO NOT SCALE DRAWING	APPROVALS	DATE	VIS Valmark Interface Solutions <sup>®</sup> A Nidec Kinetek Company	
THIRD ANGLE PROJECTION UNLESS OTHERWISE SPECIFIED, UNITS ARE IN INCHES. TOLERANCES: TOOLING: .XX ±0.01" CUT TO GRAPHICS: .XX ±0.02" .XXX ±0.010" .XXX ±0.015" ANGLES ±0.5° ANGLES ±0.5°	DRW DW 07/11/14 CHK DSN ENGR		COMPANY (OEM)	TRIMBLE
INTERPRET DRAWING PER ANSI Y14.5M -- 1994	SCALE 1:1	SHEET 1 of 1	PART NO.	94469-00
			REV	01




**Responsibility for Validation and Fitness-of-Use:**  
 Because Valmark Industries, Inc. has no control over the use or application of these parts, it is the sole responsibility of the OEM customer and/or its designated manufacturer to test all custom parts for fitness-of-use and validation of design prior to acceptance of production units. Valmark Industries provides expertise in the layout and consistent fabrication of high quality, reliable membrane switch, custom graphics and labeling products. Valmark and its employees do NOT purport to be experts in the end-use application of our customers, or the environments in which these products will be stored and/or used.

THIS PRINT MUST BE APPROVED AND RETURNED WITHIN 24 HOURS IN ORDER FOR THIS JOB TO PROCEED WITH PRODUCTION. ACCEPTANCE OF THE BELOW ART SAMPLE RELEASES VALMARK OF ANY GRAPHICS LIABILITY AFTER THE PRODUCTION RUN. (1) Valmark may, at its discretion unless otherwise noted, substitute any materials or BOM components with equivalent or similar materials and/or components based on control of cost or availability

Customer Supplied Prints			
	Part Number	Date	
Dimensional			
Graphics			
Modifications			
Rev.	ECO #	Description	Date

DETAILED DIMENSIONS ARE IN THE CUSTOMER SUPPLIED DRAWING



APPROVAL PRINT

RESUBMIT WITH CORRECTIONS

APPROVED WITH CORRECTIONS

OK AS IS

APPROVAL SIGNATURE \_\_\_\_\_ DATE \_\_\_\_\_

NOTES:	CONSTRUCTION:
1 LABEL PERIPHERY-keyline does not print	BASE MATERIAL .007" GE FR83-112
2 BACKGROUND: TRIMBLE MED. GREY NCS 5505-BO7G	ADHESIVE - FULL 3M 468
3 GRAPHICS: BLACK	
4 WHITE FOR OPACITY	

DO NOT SCALE DRAWING	APPROVALS	DATE	VIS Valmark Interface Solutions <sup>®</sup> A Nidec Kinetek Company	
THIRD ANGLE PROJECTION UNLESS OTHERWISE SPECIFIED, UNITS ARE IN INCHES. TOLERANCES: TOOLING: XX ±0.01" CUT TO GRAPHICS: XX ±0.02" XXX ±0.010" XXX ±0.015" ANGLES ±0.5° ANGLES ±0.5°	DRW DW 07/11/14 CHK DSN ENGR		COMPANY (OEM)	TRIMBLE
INTERPRET DRAWING PER ANSI Y14.5M -- 1994	SCALE 1:1	SHEET 1 of 1	PART NO.	94469-60
				REV 01




**Responsibility for Validation and Fitness-of-Use:**  
 Because Valmark Industries, Inc. has no control over the use or application of these parts, it is the sole responsibility of the OEM customer and/or its designated manufacturer to test all custom parts for fitness-of-use and validation of design prior to acceptance of production units. Valmark Industries provides expertise in the layout and consistent fabrication of high quality, reliable membrane switch, custom graphics and labeling products. Valmark and its employees do NOT purport to be experts in the end-use application of our customers, or the environments in which these products will be stored and/or used.

THIS PRINT MUST BE APPROVED AND RETURNED WITHIN 24 HOURS IN ORDER FOR THIS JOB TO PROCEED WITH PRODUCTION. ACCEPTANCE OF THE BELOW ART SAMPLE RELEASES VALMARK OF ANY GRAPHICS LIABILITY AFTER THE PRODUCTION RUN. (1) Valmark may, at its discretion unless otherwise noted, substitute any materials or BOM components with equivalent or similar materials and/or components based on control of cost or availability

Customer Supplied Prints			
	Part Number	Date	
Dimensional			
Graphics			
Modifications			
Rev.	ECO #	Description	Date

DETAILED DIMENSIONS ARE IN THE CUSTOMER SUPPLIED DRAWING



APPROVAL PRINT

RESUBMIT WITH CORRECTIONS

APPROVED WITH CORRECTIONS

OK AS IS

APPROVAL SIGNATURE \_\_\_\_\_ DATE \_\_\_\_\_

NOTES:	CONSTRUCTION:
1 LABEL PERIPHERY-keyline does not print	BASE MATERIAL .007" GE FR83-112
2 BACKGROUND: TRIMBLE MED. GREY NCS 5505-BO7G	ADHESIVE - FULL 3M 468
3 GRAPHICS: BLACK	
4 WHITE FOR OPACITY	

DO NOT SCALE DRAWING	APPROVALS	DATE	Valmark Interface Solutions <sup>®</sup> A Nidec Kinetek Company	
THIRD ANGLE PROJECTION UNLESS OTHERWISE SPECIFIED, UNITS ARE IN INCHES. TOLERANCES: TOOLING: .XX ±0.01" CUT TO GRAPHICS: .XX ±0.02" .XXX ±0.010" .XXX ±0.015" ANGLES ±0.5° ANGLES ±0.5°	DRW DW 06/26/14 CHK DSN ENGR		COMPANY (OEM)	TRIMBLE
INTERPRET DRAWING PER ANSI Y14.5M -- 1994	SCALE 1:1	SHEET 1 of 1	PART NO.	94469-91
			REV	01