

VISION

The Ultimate in Car Security

TAIWAN

TEL : 886-6-255-1289

247-0776


FAX : 886-6-255-4484

P.O. : 34-26 TAINAN

TAIWAN, R.O.C.

E-mail : business@ma8.hinet.net

1. To Change R7 value. (1k Ohm \rightarrow 47k Ohm)
2. Add a capacitor (22nF) between R7 and Himark TX4915 IC.



Wang Tsung Chin

Wang Tsung Chin / Engineer
Vision Automobile Elect. Ind. Co., Ltd.