

15 March 2010

Federal Communications Commission Authorization and Evaluation Division

Re: Adjustment of the Model DSP85-U7C In-building Amplifier in the Field

The CSI Model DSP85-U7C In-Building Amplifier offers only adjustment of gain (below its factory-set maximum gain level) to the technician during installation and maintenance activities. This adjustment is dependent on the physical environment in which the amplifier is to be installed and is described in the Installation and Users Manual. This is the only adjustment accessible without opening the amplifier. Frequency response and gain thresholds are factory set and in no circumstance are they to be adjusted in the field.

Regards,

Burt Salkins

**Burt Salkins** 

Director of Engineering