



Group 4 Technology Limited,
Challenge house,
International Drive,
Tewkesbury,
Gloucestershire,
G120 8UQ

01684 850977

15/01/2007

Differences between the Proxi pen 2 and Proxi Pen 2 MK II

The Proxi pen 2 MK II has an additional 5V power supply (the original unit only had a 3.3V supply), this is used to power the tag detect and sounder circuit.

The CPLD used in the Proxi Pen 2 has been removed and implemented with discrete logic. This affects the tag-detect, proximity transceiver and demodulation circuits

The layout of the PCB has been modified to accommodate these changes.

There have been no other modifications.