

Probe ET3DV6

SN: 1560


Manufactured:
Calibrated:

December 1, 2000
February 20, 2002

Calibrated for System DASY3

PCTEST Calibration Laboratory

Approved By:



Alfred Cirwithian
Vice President Engineering

ET3DV6 SN: 1560

DASY3 – Parameters of Probe: ET3DV6 SN:1560

Sensitivity in Free Space

NormX **1.48** $\mu\text{V}/(\text{V}/\text{m})^2$
NormY **1.51** $\mu\text{V}/(\text{V}/\text{m})^2$
NormZ **1.43** $\mu\text{V}/(\text{V}/\text{m})^2$

Diode Compression

DCP X 98 mV
DCP X 98 mV
DCP X 98 mV

Sensitivity in Tissue Simulating Liquid

Head **835 MHz Brain** $e_r = 41.5 \pm 5\%$ $s = 0.90 \pm 5\% \text{ mho/m}$

ConvF X = **6.78**
ConvF Y = **6.78**
ConvF Z = **6.78**

Boundary Effect:
Alpha **0.30**
Depth **2.90**

Body **835 MHz Brain** $e_r = 56.2 \pm 5\%$ $s = 0.95 \pm 5\% \text{ mho/m}$

ConvF X = **6.52** $\pm 7\%$ (k=2)
ConvF Y = **6.52** $\pm 7\%$ (k=2)
ConvF Z = **6.52** $\pm 7\%$ (k=2)

Boundary Effect:
Alpha **0.30**
Depth **2.90**

Head **1900 MHz Brain** $e_r = 40.0 \pm 5\%$ $s = 1.40 \pm 5\% \text{ mho/m}$

ConvF X = **5.16**
ConvF Y = **5.16**
ConvF Z = **5.16**

Boundary Effect:
Alpha **0.48**
Depth **2.40**

Body **1900 MHz Muscle** $e_r = 54.2 \pm 5\%$ $s = 1.50 \pm 5\% \text{ mho/m}$


ConvF X = **4.70** $\pm 7\%$ (k=2)
ConvF Y = **4.70** $\pm 7\%$ (k=2)
ConvF Z = **4.70** $\pm 7\%$ (k=2)

Boundary Effect:
Alpha **0.48**
Depth **2.40**


Sensor Offset



Probe Tip to Sensor Center **2.7** mm
Optical Surface Detection **2.0 $\pm$ 0.2** mm

ET3DV6 SN:1560



Isotropy Error (ϕ), $\theta = 0^\circ$





Conversion Factor Assessment for *DASY3* SAR Measurement System

ET3DV6 S/N: 1560

835 MHz Brain

$$\epsilon_r = 42 \pm 5\%$$

$$s = 0.90 \pm 5\% \text{ mho/m}$$

$$\text{ConvF X} = 6.78 \pm 7\% (k=2)$$

$$\text{ConvF Y} = 6.78 \pm 7\% (k=2)$$

$$\text{ConvF Z} = 6.78 \pm 7\% (k=2)$$

Boundary Effect:

$$\text{Alpha} \quad 0.30$$

$$\text{Depth} \quad 2.90$$

1900 MHz Brain

$$\epsilon_r = 40 \pm 5\%$$

$$s = 1.40 \pm 5\% \text{ mho/m}$$

$$\text{ConvF X} = 5.16 \pm 7\% (k=2)$$

$$\text{ConvF Y} = 5.16 \pm 7\% (k=2)$$

$$\text{ConvF Z} = 5.16 \pm 7\% (k=2)$$

Boundary Effect:

$$\text{Alpha} \quad 0.48$$

$$\text{Depth} \quad 2.40$$

Schmid & Partner Engineering AG

Zughausstrasse 43, 8004 Zurich, Switzerland, Phone +41 1 245 97 00, Fax +41 1 245 97 79

Certificate of conformity / First Article Inspection

Item	SAM Twin Phantom V4.0
Type No	QD 000 P40 BA
Series No	TP-1002 and higher
Manufacturer / Origin	Untersee Composites Hauptstr. 69 CH-8559 Fruthwilen Switzerland

Tests

The series production process used allows the limitation to test of first articles.
Complete tests were made on the pre-series Type No. QD 000 P40 AA, Serial No. TP-1001 and on the series first article Type No. QD 000 P40 BA, Serial No. TP-1006. Certain parameters have been retested using further series units (called samples).

Test	Requirement	Details	Units tested
Shape	Compliance with the geometry according to the CAD model.	IT'IS CAD File (*)	First article, Samples
Material thickness	Compliant with the requirements according to the standards	2mm +/- 0.2mm in specific areas	First article, Samples
Material parameters	Dielectric parameters for required frequencies	200 MHz - 3 GHz Relative permittivity < 5 Loss tangent < 0.05.	Material sample TP 104-5
Material resistivity	The material has been tested to be compatible with the liquids defined in the standards	Liquid type HSL 1800 and others according to the standard.	Pre-series, First article

Standards

- [1] CENELEC EN 50361
- [2] IEEE P1528-200x draft 6.5
- [3] IEC PT 62209 draft 0.9
- (*) The IT'IS CAD file is derived from [2] and is also within the tolerance requirements of the shapes of [1] and [3].


Conformity

Based on the sample tests above, we certify that this item is in compliance with the uncertainty requirements of SAR measurements specified in standard [1] and draft standards [2] and [3].

Date

18.11.2001

Signature / Stamp



**Schmid & Partner
Engineering AG**



Zughausstrasse 43, CH-8004 Zurich
Tel. +41 1 245 97 00, Fax +41 1 245 97 79