

1

2


3

4

5

Scale/1:1
Unit/mm
DO NOT SCALE DRAWING

REV.	ZONE	DATE	EXPLAIN



Lot的規則
SER(LL 訂單號碼)-流水碼
 [Mir][LL PO]-[Lot / Box]
 For example, if Sercomm were building a Lot under Link Labs Purchase Order PO-00000696, box number 9 would be labeled as follows:
 SER00000696-009

- (28P) Link Labs Model Name
- (1P) Model Number
- (16S) Manufacturer's Part Number(use Sercomm Model Number)
- (10D) Date Code(format: YYWW)
- (Q) Quantity
- (4L) Country of Origin (two-character ISO 3166 country code)
- (1T) A list containing each Lot Number contained therein(e.g. *SER00000626-009*)

QR barcode :7x7mm
 BT MAC: A1:B2:C3:D4:E5:F6
 (MAC地址顯示的資訊英文字母必須為大寫)

1*單位用量 (Unit dosage)*1




- 底色 (Background) Color=>Black C
- 藍色線條/字樣為工廠列印辨識使用
Blue lines / typefaces are used for factory print identification
- 紅框為刀模線不印刷(The red frame is not printed for the die line)

- Notes:
- 材質: 50#白色Mylar,上打字用霧膜PET
Material: 50 # white Mylar, fog film PET for typing
 - 背壓花膠/成捲
Back embossed gelatin / roll
 - 尺寸/印刷:如圖示
Size / printing: as shown
 - 方框內尺寸為重點檢驗尺寸
The size in the box is the key inspection size
 - 公差:+0,- 0.2mm
Tolerance: + 0,-0.2mm
 - 本料件使用之材料須符合RoHS
The materials used in this part must be RoHS compliant

FCC ID: P27SMATK02
IC: 12201A-ATK02

來料方式 (Incoming method)



DO NOT SCALE DRAWING

CONFIDENTIAL PROPRIETARY			Tooling Name	
MODEL	SM-ATK02	NAME	Link Labs,Product Label	
DSN		PART. NO	932DEC02	
CHK		MATERIAL		Q'TY 1 /PC
APV		SERCOMM		REV. A
FILE	SERCOMM			REV. DATE