





Liquid depth in the flat Phantom (835 MHz, 15.1cm depth)



Liquid depth in the head Phantom (835 MHz, 15.0cm depth)




Liquid depth in the flat Phantom (1900 MHz, 15.2cm depth)




Liquid depth in the head Phantom (1900 MHz, 15.1cm depth)




Liquid depth in the flat Phantom (2450 MHz, 15.1cm depth)




Liquid depth in the head Phantom (2450 MHz, 15.0cm depth)




Right Head Tilt Setup Photo




Right Head Cheek Setup Photo




Left Head Tilt Setup Photo



Left Head Cheek Setup Photo



5mm Body-worn Accessory& Hotspot Mode Rear Side Setup Photo



5mm Body-worn Accessory& Hotspot Mode Front Side Setup Photo



10mm Hotspot Mode Top Edge Setup Photo



10mm Hotspot mode Bottom Edge Setup Photo



10mm Hotspot mode Left Edge Setup Photo



10mm Hotspot mode Right Edge Setup Photo