


**Mealstream EC501 (Series 5) CTM3 208V, 60Hz
FCC Class II permissible Change**

EMC Test Set-up: Conducted Emissions



**Mealstream EC501 (Series 5) CTM3 208V, 60Hz
FCC Class II permissible Change**

EMC Test Set-up: Radiated Emissions - Pre-scan @ approx. 1 metre



EUT

**Mealstream EC501 (Series 5) CTM3 208V, 60Hz
FCC Class II permissible Change**

EMC Test Set-up: Radiated Emissions Open Area Test Site 10m and 3m



@ 10 metre



@ 3 metre