



Mattel Asia Pacific Sourcing Limited

美泰玩具亞太有限公司

20-Sep-2006

To Whom It May Concern:


This letter is providing the additional information for the Permissive Change application. The model Hyper Scan K4386 is based on the previously original certified model Hyper Scan K4386.

Following are the change made:

1. The adaptor bundled is changed from 6V, 700mA to 7.5V, 500mA
 2. Use new PCBA with heat sink plates.
-

All design including electronic, electrical and construction remain the same except the above mentioned. The above specified change is not intended for maximum power.

Sincerely,



Ivan CW Chang
Staff Engineer