

Hortau Inc.
735 rue de l'Église,
St-Romuald, Qc
Canada, G6W 5M6

Object: Differences between Irrolis Sense Tx models.

Our Irrolis Sense Tx family product includes three models: Tx-07, Tx-35 and Tx-80. The difference between the models is the range of the pressure sensor used in the probe and the transmission interval. The range of readings and transmission intervals are as follow:

Tx-07 = 0 to 7 KPa of tension (transmissions occur every 120 seconds)

Tx-35 = 0 to 35 KPa of tension (transmissions occur every 300 seconds)

Tx-80 = 0 to 80 KPa of tension (transmissions occur every 300 seconds)

Sincerely



Philippe Jobin
R-D Director
Hortau Inc.