

Difference Description for Acclarix LX9 Series Products

Acclarix LX9, Acclarix LX9 Exp, Acclarix LX9 Super, Acclarix LX85, Acclarix LX88(They have the same circuit principle, appearance and performance, but they are different for different customer configurations .Since only the measurement configuration (software function) of Acclarix LX9 is different from other models, and it does not affect the wireless test, so, we choose the Acclarix LX9 as the DUT (device under test) to cover all the models.)

The configuration differences are listed in table 1 below.

Table 1 Configuration Difference between each Model

	Product type	Configuration differentia		
		Func.1	Func.2	Func.3
		Seminal Vesicle Measurement	Testis Measurement	One key footswitch
Acclarix LX9 Series	Acclarix LX9	X	√	√
	Acclarix LX9 Exp	√	X	√
	Acclarix LX9 Super	√	√	√
	Acclarix LX85	X	√	X
	Acclarix LX88	√	X	X

'X' represents "could not be supported";

'√' represents "could be supported".

Huanhuan Xia
EDAN INSTRUMENTS, INC.