

CenTrak Virtual Wall IT-323*



IT-323 CenTrak Virtual Wall Monitor



IT-323 CenTrak Virtual Wall
shown mounted to a ceiling

- No physical wall or curtain needed to limit area being divided
- Semi-private room separation to accurately locate an asset or person on either side of the room
- Division of bays or bed areas typically important in ER and OR Pre-Op/Post-Op settings
- Battery operated for simple installation, up to 7 years battery life (based on configuration)
- Can be configured and monitored by central server for superior control
- Simple to install clip-on ceiling mounting bracket

The Virtual Wall is a Gen2IR (infrared) signaling unit used with IR-enabled tags to provide a method of locating tagged assets or people for facilities that require sub-room level accuracy. Virtual Walls are geared to semi-private rooms and bays typically found in ER and OR settings. Unlike room-level monitors, Virtual Walls do not need physical walls to limit the area of coverage.

About CenTrak Hybrid RTLS Technology™

The CenTrak core RTLS differs from legacy in its combined use of a patented second-generation infrared (Gen2IR™) and active RFID technology. Battery powered monitors transmit a unique room number using Gen2IR, which is received by any tag in that room. The tag communicates the room number and its own unique ID via RF to the CenTrak Location Server using a hospital's existing wired or WiFi network, where it can be accessed in real-time by hospital personnel and integrated with third party solution providers.

CenTrak, Inc.
5 Caufield Place, Suite 102
Newtown, PA 18940
t: 215-860-2928
e: sales@centrak.com
www.centrak.com

**IT-323 is for use with the CenTrak 2.0 system. Order IT-321 for use with the 1.0 system.*

CenTrak Virtual Wall IT-323*

Technical Specifications



IT-323 CenTrak Virtual Wall Monitor



IT-323 CenTrak Virtual Wall shown mounted to ceiling

Operation

FCC Operating Frequency Range	902-928 MHz (Model #IT-323)*
CE Operating Frequency Range	868-870 MHz (Model #ITEU-323)*
Power Control	Local on/off, Remote on/off
Default Setting	Factory set location code – marked on Monitor
Indicators	None

Bay Area Coverage

Maximum Room Size	14' long x 12' wide (12' high)**
Minimum Room Size	8' long x 6' wide (7' high)**
Wall Thickness	Up to 1'

Product Dimensions

Base Width	5.5 in (139.7 mm)
Base Length	8.5 in (215.9 mm)
Base Depth	1.5 in (38.1 mm)
Base Weight	18.5 oz (0.53 kg)
Mounting	Ceiling tile clip, above ceiling tile

Environmental

Operating Temperature	0 C to +50 C
Storage temperature	-20 C to +70 C
Operating Humidity	10% to 90% non-condensing

Power

Battery type	Pre-installed 2xD Lithium (Extra battery pack available). Up to 3-7 years battery life based on configuration
--------------	---

*IT-323 is for use with the CenTrak 2.0 system. Order IT-321 for use with the 1.0 system.

THIS DEVICE COMPLIES WITH PART 15 OF THE FCC RULES AND INDUSTRY CANADA LICENSE-EXEMPT RSS STANDARD(S). OPERATION IS SUBJECT TO THE FOLLOWING TWO CONDITIONS: (1) THIS DEVICE MAY NOT CAUSE HARMFUL INTERFERENCE, AND (2) THIS DEVICE MUST ACCEPT ANY INTERFERENCE RECEIVED, INCLUDING INTERFERENCE THAT MAY CAUSE UNDESIRE OPERATION. Modifying or tampering with the transceiver's or receiver's internal components can cause a malfunction, invalidate the warranty, and will void FCC authorization to use these products. This product or its systems are covered by one or more of the following U.S. patents: 5,917,425, 7,061,428, 7,378,964, 7,619,532

L' utilisation de ce dispositif est autorisée seulement aux conditions suivantes : (1) il ne doit pas produire de brouillage et (2) l' utilisateur du dispositif doit être prêt à accepter tout brouillage radioélectrique reçu, même si ce brouillage est susceptible de compromettre le fonctionnement du dispositif.

CenTrak, Inc.
5 Caulfield Place, Suite 102
Newtown, PA 18940
t: 215-860-2928
e: sales@centrak.com
www.centrak.com

CenTrak Virtual Wall IT-323* Accessories



IT-323 CenTrak Virtual Wall Monitor



IT-323 CenTrak Virtual Wall
shown mounted to ceiling

Ceiling Attachments



ITA-371 VW Monitor
Ceiling Attachment
(9/16 inch)



ITA-372 VW
Monitor Ceiling
Attachment (15/16
inch) Standard



ITA-373 VW
Monitor Ceiling
Attachment
(15/16 inch) Long

Power



ITA-356
D Cell Lithium
Battery (2)
(for illustration
purposes only)



ITA-357
2D Cell Lithium
Batteries in
Pack for VW
Monitor (2
pack)



ITA-365 VW Monitor & Battery Pack Connector Cable (1 pack)

ITA-367 VW Monitor & Battery Pack Connector Cable (2 pack)



ITA-359
IR Regenerator
VW Monitor

IR Blocker



ITA-366 VW Monitor IR
Blocker – 4 inch

CenTrak, Inc.
5 Caufield Place, Suite 102
Newtown, PA 18940
t: 215-860-2928
e: sales@centrak.com
www.centrak.com

**IT-323 is for use with the CenTrak 2.0 system. Order IT-321 for use with the 1.0 system.*