



December 5, 2006

The following describes the differences and similarities between the single and dual channel Symbiq infusers:

Differences between single and dual channel infusers

The dual channel infuser includes the following changes relative to the single channel infuser.

- A second infuser channel has been added on the right side of the pump. This infuser channel is identical to the single channel on the left side of the pump with a mirrored housing.
  - o Additional power draw
  - o Delivery capability to use both channels at the same time
- The membrane switch has an additional button for right channel load/eject of the cassette loader
- The connectology has been modified to accommodate the right channel and to provide the capability for 2 infusers to be connected together.

Similarities between single and dual channel infusers

The dual channel and single channel infusers share the following common features and subsystems

- Central enclosure – The central enclosure of both infusers is identical including LCD, Touchscreen, UIC, battery, power supply, PSC, Connectivity Engine Assembly (wireless radio), and wireless antennas.
- Left infuser

Sincerely,

A handwritten signature in black ink, appearing to read "Mozammil Awan".

Mozammil Awan  
Manager, Advanced Engineering  
Hospira  
755 Jarvis Drive  
Morgan Hill, CA 95037