

PHOTOGRAPHS OF THE TEST SET-UP

Photo 1: Measurement System DASY5



Photo 2: Front View



Photo 3: Rear View



Photo 4: Left hand touched




Photo 5: Left hand tilted 15°



Photo 6: Right hand touched



Photo 7: Right hand tilted 15°



Photo 8: Front Side 15mm



Photo 9: Back Side 15mm



Photo 10: Front Side 10mm



Photo 11: Back Side 10mm



Photo 12: Left Side 10mm



Photo 13: Right Side 10mm



Photo 14: Top Side 10mm



Photo 15: Bottom Side 10mm



N/A

N/A

Photograph: Liquid depth

Photo 16: HSL850 Depth (15.1cm)




Photo 17: HSL1900 Depth (15cm)




Photo 18: HSL2450 Depth (15.0cm)



Photo 19: Body 850 Depth (15.0cm)




Photo 20: Body1900 Depth (15.0cm)



Photo 21: Body2450 Depth (15.0cm)

