




Model: Clip SMA (2.4GHz)
MAC ID: 000D6F000160111C
FCC ID: WP3CLIPMCWSMA
IC: 1467C-CLIPMCWSMA

S/N:

3011019282



© 2008 Vivonic

 **Visonic**

Model: MCT-302 SMA (2.4GHz)

FCC ID: WP3MCT302SMA
IC: 1467A-MCT302SMA

MAC ID: 000D6F0001601721

S/N: 3011019695



5-304208 312V #



**WIRELESS PHOTOELECTRIC
HEAT & SMOKE DETECTOR**
 TYPE: MCT-427 SMA(2.4GHz)

FCC ID:WP3MCT427SMA
 IC:1467C-MCT427SMA

Battery type: Panasonic CR-123A
 Refer to instal.manual: D-302151,Rev.1, 04/11


For Household Use Only
 THIS DETECTOR IS FOR SMOKE DETECTION USE
 ONLY. FOR SAFETY INFORMATION AND
 INSTRUCTIONS REFER TO MANUAL.

**WARNING: CONSTANT EXPOSURES TO HIGH OR
 LOW TEMPERATURES OR HIGH HUMIDITY
 MAY REDUCE BATTERY LIFE.**

Test the detector for correct operation using the
 test facility, whenever the battery is replaced.
 The sensitivity range is 1%/ft ~2.5%/ft

Temperature 60°C(140°F)
 For Repair return to the place of
 purchase or return to Visonic.
 Habarzel 24 Tel-aviv
 61220,ISRAEL.

S-204588 REV 00

MCT-427 SMA (2.4Ghz)
 Production date: 2011/11/03
 P/N:90-204273
 S/N: 4111962903

 S-204588 REV 00

MAC ID:
 000D6F0001600DF1

S-204588 REV 00

Operating Voltage -9V DC battery.
Battery type: Lithium battery (Ultralife #U9VL, U9VL-J).
Alkaline battery (Energizer #522,9V)

⚠ WARNING Use only batteries specified in marking. Use of a different battery may have detrimental effect on alarm operation.

⚠ WARNING Constant exposures to high or low temperature or high-humidity may reduce battery life.

S-300338 REV.01

MCT-442 SMA (2.4GHZ)
Production date: 2011/11/01
P/N:90-204272

S/N: 4111963047



S-204589 REV.00

Model Number: Supervised Indoor Wireless CO Gas Detector MCT-442 SMA(2.4GHz)

⚠ WARNING Carbon monoxide can not be seen or smelled but it can kill you. If alarm signal sounds:

1. Operate reset/silence button.
2. Call your emergency services (fire department or 911).
3. Immediately move to fresh air – outdoors or by an open door/window.

Dip SW function:

Sw. 1: ON- UL

Standard.

Sw. 1: OFF- EN

Standard.

Sw. 2: NOT USED.



FCC ID: WP3MCT442SMA
IC:1467C-MCT442SMA

CAUTION: Read installation instructions. REMINDER

- ⌋ Press the detector's test button once every week. Press the test button until the built-in buzzer sounds and the LEDs flashes sequentially.
- ⌋ Once a month, use a vacuum cleaner to clean the air vents to keep them free of dust.
- ⌋ Replace battery once a year or when a yellow LED flashes & buzzer beeps once in 60 second.
- ⌋ For information contact: Visionic INC. (USA)
West Dudley Town Rd. 65 Bloomfield, CT 06902
Phone: (860) 243-0833

This device complies with part 15 of the FCC rules. Operation

is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

S-303491 REV.00

MAC ID:

000D6F00016964B4

S-204589 REV.00



Visonic



Model: MCT-550 SMA (2.4GH)

FCC ID: WP3MCT302SMA

IC: 1467A-MCT302SMA

MAC ID:

000D6F00016014DA

S/N:

3011019470



S-20-4582 REV 00



MODEL: NEXT PLUS K9-85 SMA (2.4GHz)

MAC ID: 000D6F0001B28AB4


Contains: FCC ID: WP3ZBT

IC: 1467C-ZBT

Refer to Inst D-303361 rev.3 10/11.

S/N:

3811034122



S-20458A REV B2