











Test Positions

<p>Left Cheek</p>  A close-up photograph of the left side of the device. A silver metal rod is positioned horizontally across the top, resting on a white plastic structure. Below the rod, there are two green rectangular components and a white circular knob. The background is slightly blurred, showing other parts of the device.	<p>Left Tilt 15 Degree</p>  A close-up photograph of the left side of the device, tilted at a 15-degree angle. The silver metal rod is now angled downwards. The green rectangular components and the white circular knob are still visible, but their orientation has changed due to the tilt.
<p>Right Cheek</p>  A close-up photograph of the right side of the device. The silver metal rod is positioned horizontally across the top. The white plastic structure, green rectangular components, and white circular knob are visible from this perspective.	<p>Right Tilt 15 Degree</p>  A close-up photograph of the right side of the device, tilted at a 15-degree angle. The silver metal rod is angled downwards. The green rectangular components and the white circular knob are visible, showing the effect of the tilt on the right side.
<p>Front Side (Separation distance of 10mm)</p>  A close-up photograph of the front side of the device. The silver metal rod is positioned horizontally across the top. The white plastic structure, green rectangular components, and white circular knob are clearly visible. The separation distance between the rod and the structure is 10mm.	<p>Back Side (Separation distance of 10mm)</p>  A close-up photograph of the back side of the device. The silver metal rod is positioned horizontally across the top. The white plastic structure, green rectangular components, and white circular knob are visible from this perspective. The separation distance between the rod and the structure is 10mm.

FCC ID: ZSHA8

<p>Left Side (Separation distance of 10mm)</p>	<p>Right Side (Separation distance of 10mm)</p>
	
<p>Top Side (Separation distance of 10mm)</p>	<p>Bottom Side (Separation distance of 10mm)</p>
	

END